

Menu Route Map

NOTE

- Red color values indicate the default settings.
- The setting items or setting values with "*" may not be displayed depending on the availability of the optional accessories and other settings.

See the User's Guide for details on settings.

[Setup] Menu

Control Menu

- Sleep Mode
 - High (Deep Sleep)
 - Mid (Printer Sleep)
- Sleep Even if Error
 - Off
 - On
- Deep Sleep Eco Prior
 - Off
 - On
- Auto Sleep Time
 - 5 min.
 - 10 min.
 - 15 min.
 - 30 min.
 - 60 min.
 - 120 min.
- Sleep When Using USB*
 - Do Not Allow
 - Allow
- Timer Settings
 - Wake Up Timer
 - Off
 - On
 - Wake Up Time
 - 00:00 AM/PM to 12:00 PM to 11:59 AM/PM (00:00 to 12:00 to 23:59)
 - Auto Reset Time
 - Off
 - 10 sec.
 - 20 sec.
 - 30 sec.
 - 40 sec.
 - 50 sec.
 - 1 min.
 - 2 min.
 - 3 min.
 - 4 min.
 - 5 min.
 - 6 min.
 - 7 min.
 - 8 min.
 - 9 min.
 - Sleep Timer
 - Off
 - On
 - Sleep Time
 - 00:00 AM/PM to 12:00 PM to 11:59 AM/PM (00:00 to 12:00 to 23:59)
- Auto Skip Error
 - Off
 - On
- Language
 - Čeština
 - Dansk
 - Deutsch
 - English
 - Español
 - Français
 - Italiano
 - Magyar
 - Nederlands
 - Norsk
 - Polski
 - Português
 - Русский
 - Suomi
 - Svenska
 - Türkçe
 - 中文 (简体)
 - 한국어
- Alarm
 - Off
 - On

- Show Warnings
 - Chk/Chg. Toner Cart.
 - Off
 - On
 - Drawer Empty
 - Off
 - On
 - E-Mail Trans. Error
 - Off
 - On
- Action When Warning
 - Chk/Chg. Toner Cart.
 - Continue Printing
 - Stop Printing
- Date/Time Settings
 - Date
 - 01/01 2001 to 12/31 2030
 - 12/24 Hour Clock
 - 12 Hour (AM/PM)
 - 24 Hour
 - Time
 - 00:00:00 AM/PM to 11:59:59 AM/PM (00:00:00 to 23:59:59)
 - Daylight Savings
 - DST Settings: Off, On
 - Start Date/Time: Month, Week, Day, Time
 - End Date/Time: Month, Week, Day, Time
 - Time Zone
 - GMT-12:00 to GMT-05:00 to GMT+12:00
- Main Pwr Quick Start
 - Off
 - On
- SD Card*
 - Off
 - On
- Interrupt Print*
 - Off
 - On
- Sec. Print Del. Time*
 - 1 hr.
 - 2 hr.
 - 3 hr.
 - 6 hr.
 - 12 hr.
 - 24 hr.
- Secure Job Log*
 - Off
 - On
- USB-Connected PC OS
 - Mac OS
 - Windows
 - Other
- PDL Selection (PnP)
 - UFR II
 - UFR II (V4)
 - PCL6
 - PCL6 (V4)
 - PS3
 - XPS (Direct)
- Mng. Settings
 - Settings Key Lock
 - Off
 - On
- RMT-SW
 - Off
 - On
- Adjust Screen
 - Contrast
 - 3 to 0 to +3
 - Backlight Brightness
 - Off
 - Level 1
 - Level 2
 - Level 3

- Animated Instruction
 - Off
 - On
- Show Toner Gauge
 - Off
 - On
- Set. Comp. Notify
 - Off
 - 1 sec.
 - 2 sec.
 - 3 sec.
- Check Paper Settings
 - Off
 - On
- Scrolling Speed
 - Slow
 - Normal
 - Fast
- Canon Genuine Mode
 - Off
 - On

Paper Source

- Paper Source
 - Auto
 - Multi-Purpose Tray
 - Drawer 1
 - Drawer 2*
 - Drawer 3*
 - Drawer 4*
- MP Tray Paper Size
 - A6
 - A5
 - A5R
 - B5
 - A4
 - LTR
 - LGL
 - EXEC
 - Free Size
 - Custom Size
 - Custom Size R
 - Postcard
 - Reply Postcard
 - 4on1 Postcard
 - Env. Nagagata3
 - Env. Younaga 3
 - Env. ISO-C5
 - Env. Monarch
 - Env. No.10
 - Env. DL
 - India-LGL
 - Index Card
 - STMT
 - FLSC
 - 16K
- Drawer N Paper Size (N=1, 2, 3, 4)*
 - A6
 - A5
 - A5R
 - B5
 - A4
 - LTR
 - LGL
 - EXEC
 - Free Size
 - Custom Size
 - Custom Size R
 - India-LGL
 - STMT
 - FLSC
 - 16K
- Standard Paper Size
 - A6
 - A5

- B5
- A4
- LTR**
- LGL
- EXEC
- Postcard
- Reply Postcard
- 4on1 Postcard
- Env. Nagagata3
- Env. Younaga 3
- Env. ISO-C5
- Env. Monarch
- Env. No.10
- Env. DL
- India-LGL
- Index Card
- STMT
- FLSC
- 16K
- MP Tray Priority**
 - Off**
 - On
- MP Tray for Mix Ppr.**
 - Off**
 - On
- Auto Select Drawer**
 - Do Not Use
 - Use**
- Default Paper Type**
 - Thin 1
 - Plain 1
 - Plain 2**
 - Heavy 1
 - Heavy 2
 - Heavy 3
 - Heavy 4
 - Postcard
 - Envelope
 - Envelope H
 - Labels
 - Bond 1
 - Bond 2
 - Bond 3
- MP Tray Paper Type**
 - Thin 1
 - Plain 1
 - Plain 2
 - Heavy 1
 - Heavy 2
 - Heavy 3
 - Heavy 4
 - Postcard
 - Envelope
 - Envelope H
 - Labels
 - Bond 1
 - Bond 2
 - Bond 3
- Drawer N Paper Type (N=1, 2, 3, 4)***
 - Thin 1
 - Plain 1
 - Plain 2
 - Heavy 1
 - Heavy 2
 - Bond 1
 - Bond 2
 - Bond 3
- Mixed Types**
- Manual 2-Sided (MP)**
 - 1st Side**
 - 2nd Side
- 2-Sided Printing**
 - Off**
 - On

Network

- TCP/IP Settings**
 - IPv4 Settings**
 - IPv4: Off, **On**
 - IP Mode: **Auto**, Manual

- Protocol*
 - Use DHCP: Off, **On**
 - Use BOOTP: **Off**, On
 - Use RARP: **Off**, On
- Auto IP*: Off, **On**
- IP Address Settings
 - IP Address: **0.0.0.0** to 255.255.255.255
 - Subnet Mask: **0.0.0.0** to 255.255.255.255
 - Gateway Address: **0.0.0.0** to 255.255.255.255
- DNS
 - Primary Address: **0.0.0.0** to 255.255.255.255
 - Secondary Address: **0.0.0.0** to 255.255.255.255
- mDNS Settings*
 - mDNS: Off, **On**
 - mDNS Name*
- DHCP Option
 - Acquire Host Name: Off, **On**
 - DNS Dynamic Update: **Off**, On
- IPv6 Settings
 - IPv6: **Off**, On
 - mDNS Settings*
 - mDNS: Off, **On**
 - Use IPv4 Name (mDNS)*: Off, **On**
 - mDNS Name*
- WINS Resolution
 - Off**
 - On
- FTP
 - FTP Print: **Off**, On
 - Allow Set. via FTP: **Off**, On
- LPD Settings
 - LPD Print: Off, **On**
 - RX Timeout*: 1 to **60** (min.)
- RAW Settings
 - RAW Print: Off, **On**
 - RX Timeout*: 1 to **60** (min.)
- IPP Print
 - Off
 - On**
- WSD
 - WSD Print: Off, **On**
 - WSD Browsing*: Off, **On**
 - Multicast Discovery: Off, **On**
- HTTP
 - Off
 - On**
- Proxy Settings
 - Proxy: **Off**, On
 - Server Address*
 - Port Number*: 1 to **80** to 65535
 - Same Domain*: Use Proxy, **Do Not Use Proxy**
 - Proxy Authentication*: **Off**, On
 - User Name*
 - Password*
- SNTP
 - Off**
 - On
- Discovery Response
 - Off
 - On**
- IPSec
 - Off**
 - On
- Sleep Notif. Set.
 - Sleep Mode Notif.: Off, **On**
 - Port Number*: 1 to **11427** to 65535
 - Routers to Traverse*: 0 to **3** to 254
 - Notif. Interval*: 60 to **600** to 65535
- Mopria**
 - Off
 - On**
- Google Cloud Print**
 - Use Cloud Print: Off, **On**
 - Registration Status
- SMB***
 - SMB Server**
 - Off**
 - On
 - SMB Print***
 - Off**
 - On

- SNMP Settings**
 - SNMPv1 Settings**
 - SNMPv1: Off, **On**
 - Dctd. Community Set.
 - Dctd. Community: Off, Read/Write, **Read Only**
 - SNMPv3 Settings**
 - SNMPv3: **Off**, On
 - User Settings N (N=1, 2, 3, 4, 5)*
 - Auth. Password
 - Encryption Password
 - Rjct Packet in Sleep
 - Off**
 - On
- Spooler***
 - Off**
 - On
- Receive in Parallel**
 - Off
 - On**
- Wait Time at Startup**
 - 0** to 300 (sec.)
- Remote UI Settings**
 - Remote UI**
 - Off
 - On**
 - RUI Access Sec. Set.**
 - Off**
 - On
 - TLS***
 - Off**
 - On
- Software Regist/Updt***
 - Software Mngt. Set.**
 - Communication Test
- Ethernet Driver**
 - Auto Detect**
 - Off
 - On**
 - Communication Mode***
 - Half Duplex**
 - Full Duplex
 - Ethernet Type***
 - 10 Base-T**
 - 100 Base-TX
 - 1000 Base-T
- Sleep Mode Priority**
 - Optimal Balance**
 - Exit Speed
 - Energy Saving
- IEEE802.1X**
 - Off**
 - On
- Address Filter**
 - Off
 - On**
- MAC Address**
 - (Display only)
- E-Mail Print Set.**
 - POP3 RX Interval**
 - 0** to 90 (min.)
 - POP3 RX**
 - Off**
 - On
 - SMTP RX**
 - Off**
 - On
- Monitoring Service**
 - Comm. Test**
 - Comm. Log**
 - (Display only)
- Init. Network Set.**

Layout

- Number of Copies**
 - 1** to 9999
- Offset Y**
 - 1.97 to **0.00** to +1.97 (inches)
 - (-50.0 to **0.0** to +50.0 (mm))
- Offset X**
 - 1.97 to **0.00** to +1.97 (inches)
 - (-50.0 to **0.0** to +50.0 (mm))

Binding Location

- Long Edge**
- Short Edge

Gutter

- 1.97 to **0.00** to +1.97 (inches)
- (-50.0 to **0.0** to +50.0 (mm))

Alternative Method

- Off
- On**

Print Quality

Resolution

- 600 dpi**
- 1200 dpi

Image Refinement*

- Off
- On**

Toner Save

- Off**
- On

Density*

- 8 to **0** to +8

Density (Fine Adj)*

- High
 - 8 to **0** to +8
- Medium
 - 8 to **0** to +8
- Low
 - 8 to **0** to +8

Halftones

- Text
 - Resolution**
 - Gradation
 - Color Tone
 - High Resolution
- Graphics
 - Resolution
 - Gradation
 - Color Tone**
 - High Resolution
- Image
 - Resolution
 - Gradation
 - Color Tone**
 - High Resolution

Reduce Quality

- Continue Printing**
- Stop Printing

Adj. Prt. Line Width

- 7 to **0** to +8

Interface

Interface Selection

- USB
 - Off
 - On**
- Network
 - Off
 - On**
- USB Adv. Functions
 - Adv. Func. Settings: **Meap Priority**, USB Over NW Priority
 - USB Storage Device
 - MEAP Driver: **Off**, On

Timeout

- Timeout
 - Off
 - On**
- Timeout Time*
 - 5 to **15** to 300 (seconds)

Connection Recog.

- Off
- On**

Extended RX Buffer

- Off
- On**

User Maintenance

Adj. Print Position

- Common
 - Offset Y (2-Sided)
 - -0.20 to **0.00** to +0.20 (Inches)
 - (-5.0 to **0.0** to +5.0 (mm))
 - Offset X (2-Sided)
 - -0.20 to **0.00** to +0.20 (Inches)
 - (-5.0 to **0.0** to +5.0 (mm))
- Multi-Purpose Tray
 - Offset Y (MP Tray)
 - -0.20 to **0.00** to +0.20 (Inches)
 - (-5.0 to **0.0** to +5.0 (mm))
 - Offset X (MP Tray)
 - -0.20 to **0.00** to +0.20 (Inches)
 - (-5.0 to **0.0** to +5.0 (mm))
- Drawer 1 to 4*
 - Offset Y (Drawer 1 to 4)
 - -0.20 to **0.00** to +0.20 (Inches)
 - (-5.0 to **0.0** to +5.0 (mm))
 - Offset X (Drawer 1 to 4)
 - -0.20 to **0.00** to +0.20 (Inches)
 - (-5.0 to **0.0** to +5.0 (mm))

Recovery Printing

- Off
- On**

Check Paper Size

- Off**
- On

Substitute Size

- Off**
- On

Short Edge Fd. Prty.

- Off**
- On

Sp. Transfer Mode

- Off**
- On

Special Print Mode A

- Off
- Mode 1**
- Mode 2
- Mode 3
- Mode 4

Adj. Scndry Transfer

- Off**
- On

Wrinkle Correction

- Off**
- On

Afterimage Corr.

- Off**
- On

Sp. Transfer Mode 2

- Off**
- On

Special Deliv. Mode

- Off**
- On

Improve Toner Fixing

- Off**
- On

SD Card Maintenance*

- Format
- Completely Del. Data

Special Print Mode

- Curl Correction
 - Off**
 - On
- Reduce Ppr. Sticking
 - Off**
 - On
- Rough Paper Adj.
 - Off**
 - On
- 2-Sd Prnt Speed Prty
 - Off**
 - On
- Incr Pcard Fix. Qlty
 - Off**
 - On

Special Print Adj. C

- Off**
- On

Update Firmware

- USB
- Network

Paper Feed Method

- Multi-Purpose Tray
 - Speed Priority**
 - Print Side Priority
- Drawer 1 to 4*
 - Speed Priority**
 - Print Side Priority

Show Job List

- Off
- On**

Rdc Thin Ppr Curling

- Off**
- On

Import/Export Set.

- IMPORT
- EXPORT

Notify to Clean

- Off**
- On

Clean. Notif. Timing*

- 1000** to 50000 (pages)

Toner Check Timing

- Default**
- Custom

Spec Tnr Chk Timing*

- 1 to **20** to 99 (%)

Control Condensation

- Off**
- On

Rdc Drk Afrt Cart Ch

- Off**
- On

Print Mode

Auto Mode Selection

- Auto Selection**
- PCL
- PS
- PDF
- XPS

Auto Select

- PCL
 - Off
 - On**
- PS
 - Off
 - On**
- PDF
 - Off
 - On**
- XPS
 - Off
 - On**

Mode Priority

- None**
- PCL
- PS
- PDF
- XPS

UFR II

- Paper Save**
 - Off
 - On**

PCL

- Paper Save**
 - Off**
 - On
- Orientation**
 - Portrait**
 - Landscape
- Font Number**
 - 0** to 104
- Point Size***
 - 4.00 to **12.00** to 999.75 (point)
- Pitch***
 - 0.44 to **10.00** to 99.99 (cpi)

Form Lines
5 to 60 to 128 (lines)
Character Code
PC8
ROMAN8
ROMAN9
ISOL1
ISOL2
ISOL5
ISOL6
ISOL9
PC775
PC8DN
PC850
PC852
PC858
PC8TK
PC1004
WINL1
WINL2
WINL5
WINBALT
DESKTOP
PSTEXT
LEGAL
ISO4
ISO6
ISO11
ISO15
ISO17
ISO21
ISO60
ISO69
WIN 30
MCTEXT
PC864
ARABIC8
WINARB
PC866
ISOCYR
WINCYR
PC851
GREEK8
ISOGRK
PC8GRK
WINGRK
PC862
HEBREW7
HEBREW8
ISOHEB
Custom Size
Do Not Set
Set
Unit of Measurement*
Millimeters
Inches
X Dimension*
2.99 to 8.50 in. (76.0 to 215.9 to 216.0 mm)
Y Dimension*
5.00 to 14.00 to 14.02 in. (127.0 to 355.6 to 356.0 mm)
Append CR to LF
Yes
No
Enlarge A4 Prt Width
Off
On
BarDIMM*
Enable
Disable
FreeScale*
Off
~
"
#
\$
/
\
?
{
}

Imaging
Image Orientation
Auto
Vertical
Horizontal
Zoom
Off
Auto
Print Position
Auto
Center
Top Left
TIFF Spooler
Off
On
Show Warnings
Off
Print
Panel
Print E-Mail Text
Off
On
Limit E-Mail Print*
Off
On
Enlarge Print Area
Off
On
Halftones
Resolution
Gradation
High Resolution
Grayscale Conversion
sRGB
NTSC
Uniform RGB

XPS
Halftones
Text
Resolution
Gradation
High Resolution
Graphics
Resolution
Gradation
High Resolution
Image
Resolution
Gradation
High Resolution
Grayscale Conversion
Text
sRGB
NTSC
Uniform RGB
Graphics
sRGB
NTSC
Uniform RGB
Image
sRGB
NTSC
Uniform RGB
Compressed Img Mode*
Image Priority
Output Priority
Compressed Img Outpt
Output
Display Error

PDF
Fit to Paper Size
Off
On
Enlarge Print Area
Off
On

N on 1
Off
2 on 1
4 on 1
6 on 1
8 on 1
9 on 1
16 on 1
Comment Print
Off
Auto
Halftones
Text
Resolution
Gradation
High Resolution
Graphics
Resolution
Gradation
High Resolution
Image
Resolution
Gradation
High Resolution
Grayscale Conversion
sRGB
NTSC
Uniform RGB

PS
Job Timeout
0 to 3600 (seconds)
Print PS Errors
Off
On
Halftones
Text
Resolution
Gradation
High Resolution
Graphics
Resolution
Gradation
High Resolution
Image
Resolution
Gradation
High Resolution
Grayscale Conversion
sRGB
NTSC
Uniform RGB

MEAP Settings
Select Def. Screen
Print Screen
MEAP
Use DNS Caching
Off
On (Unlimited Use)
On (Specify Period)
Period of Validity*
1 to 60 to 120 (seconds)
Add X-FRAME-OPTIONS
Off
On

Check Counter
101: Total 1
(Display only)

Initialize Menu

[Utility] Menu
Check Counter
101: Total 1
(Display only)
Configuration Page
Network Status Print

Consmbl. Status Prt.
IPSec Policy List
PCL Utility
Font List
PS Utility
Configuration Page
Font List
Cleaning
A4
LTR
E-Mail Print Utility
Received E-Mail
E-Mail RX Log List
Printing Pos. Print
Page Count List
Counter Report
Print MEAP Sys. Info
Cartridge Log Print
Serial Number
(Display only)
Consumables Info.
Paper Information
Multi-Purpose Tray: (Display only)
Drawer 1: (Display only)
Drawer 2*: (Display only)
Drawer 3*: (Display only)
Drawer 4*: (Display only)
Toner Cart. Model
(Display only)
Remaining Toner
(Display only)

[Job] Menu
Encrypted Print*
Secured Print*
Stored Job List*
Stored Job Print*
Job Print Log*
Stored Job Print Log*
Report Print Log*
E-Mail Print Log*

[Reset] Menu
Soft Reset (Hard Reset)
Form Feed
Shut Down

[Select Feeder] Menu
Paper Source
Auto
Multi-Purpose Tray
Drawer 1
Drawer 2*
Drawer 3*
Drawer 4*
MP Tray Paper Size
A6
<input type="checkbox"/> A5
<input type="checkbox"/> A5R
B5
A4
LTR
LGL
EXEC

Free Size
<input type="checkbox"/> Custom Size
<input type="checkbox"/> Custom Size R
Postcard
Reply Postcard
4on1 Postcard
Env. Nagagata3
Env. Younaga 3
Env. ISO-C5
Env. Monarch
Env. No.10
Env. DL
India-LGL
Index Card
STMT
FLSC
16K
Drawer N Paper Size (N=1, 2, 3, 4)*
A6
<input type="checkbox"/> A5
<input type="checkbox"/> A5R
B5
A4
LTR
LGL
EXEC
Free Size
<input type="checkbox"/> Custom Size
<input type="checkbox"/> Custom Size R
India-LGL
STMT
FLSC
16K
Standard Paper Size
A6
A5
B5
A4
LTR
LGL
EXEC
Postcard
Reply Postcard
4on1 Postcard
Env. Nagagata3
Env. Younaga 3
Env. ISO-C5
Env. Monarch
Env. No.10
Env. DL
India-LGL
Index Card
STMT
FLSC
16K
MP Tray Priority
Off
On
MP Tray for Mix Ppr.
Off
On
Auto Select Drawer
Do Not Use
Use
Default Paper Type
Thin 1
Plain 1
Plain 2
Heavy 1
Heavy 2
Heavy 3
Heavy 4
Postcard
Envelope
Envelope H
Labels
Bond 1
Bond 2
Bond 3

MP Tray Paper Type
Thin 1
Plain 1
Plain 2
Heavy 1
Heavy 2
Heavy 3
Heavy 4
Postcard
Envelope
Envelope H
Labels
Bond 1
Bond 2
Bond 3
Mixed Types
Drawer N Paper Type (N=1, 2, 3, 4)*
Thin 1
Plain 1
Plain 2
Heavy 1
Heavy 2
Bond 1
Bond 2
Bond 3
Mixed Types
Manual 2-Sided (MP)
1st Side
2nd Side
2-Sided Printing
Off
On