

Menu Route Map

Network Settings

- Select Wired/Wireless LAN
 - Wired LAN, Wireless LAN
- Wireless LAN Settings
 - WPS Push Button Mode
 - WPS PIN Code Mode
 - SSID Settings
 - Select Access Point
 - Enter Manually
 - Security Settings
 - None
 - WEP
 - Open System, Shared Key
 - WPA/WPA2-PSK
 - Auto, AES-CCMP
 - Power Save Mode
 - Off, On
 - Connection Information
 - MAC Address
 - Wireless LAN Status
 - Latest Error Information
 - Channel
 - SSID Settings
 - Security Settings
 - Power Save Mode
- Enable Direct Connection
 - Off, On
- TCP/IP Settings
 - IPv4 Settings
 - IP Address Settings
 - Auto Acquire
 - Select Protocol
 - Off, DHCP
 - Auto IP
 - Off, On
 - Manually Acquire
 - IP Address: 0.0.0.0
 - Subnet Mask: 0.0.0.0
 - Gateway Address: 0.0.0.0
 - Check Settings
 - Auto Acquire
 - IP Address
 - Subnet Mask
 - Gateway Address
 - PING Command
 - DNS Settings
 - DNS Server Settings
 - Primary DNS Server: 0.0.0.0
 - Secondary DNS Server: 0.0.0.0
 - DNS Host Name/Domain Name Settings
 - Host Name
 - Domain Name
 - DNS Dynamic Update Settings
 - Off, On
 - mDNS Settings
 - Off, On
 - DHCP Option Settings
 - Acquire Host Name
 - Off, On
 - DNS Dynamic Update
 - Off, On
 - Acquire DNS Server Address
 - Off, On
 - Acquire Domain Name
 - Off, On
 - Acquire WINS Server Address
 - Off, On
 - Acquire SMTP Server Address
 - Off, On
 - Acquire POP Server Address
 - Off, On
 - IPv6 Settings
 - Use IPv6
 - Off, On, Check Settings
 - Link-Local Address
 - Prefix Length
 - Stateless Address Settings
 - Off, On, Check Settings
 - Stateless Address
 - Prefix Length
 - Use DHCPv6
 - Off, On, Check Settings
 - Stateful Address
 - Prefix Length
 - DNS Settings
 - DNS Host Name/Domain Name Settings (Use IPv4 Host/Domain)
 - Off, On
 - Host Name
 - Domain Name
 - DNS Dynamic Update Settings
 - Off, On
 - mDNS Settings
 - Off, On
 - DHCP Option Settings
 - Acquire DNS Server Address
 - Off, On
 - Acquire Domain Name
 - Off, On
 - WINS Settings
 - WINS Resolution
 - Off, On (WINS Server Address: 0.0.0.0)
 - LPD Settings
 - LPD Print Settings
 - Off, On
 - RX Timeout
 - 1 to 5 to 60 (min.)
 - RAW Settings
 - RAW Print Settings
 - Off, On
 - RX Timeout
 - 1 to 5 to 60 (min.)
 - WSD Settings
 - WSD Print Settings
 - Use WSD Print
 - Off, On
 - Use WSD Browsing
 - Off, On
 - WSD Scan Settings
 - Use WSD Scan
 - Off, On
 - Use Computer Scan
 - Off, On
 - Use Multicast Discovery
 - Off, On
 - Use FTP PASV Mode
 - Off, On
 - Use HTTP
 - Off, On
 - IPP Print Settings
 - Use IPP Printing
 - Off, On
 - Use SSL
 - Off, On
 - Use Network Link Scan
 - Off, On

Port Number Settings

- LPD
 - 1 to 515 to 65535
- RAW
 - 1 to 9100 to 65535
- WSD Multicast Discovery
 - 1 to 3702 to 65535
- HTTP
 - 1 to 80 to 65535
- Multicast Discovery
 - 1 to 427 to 65535
- POP3
 - 1 to 110 to 65535
- SMTP
 - 1 to 25 to 65535
- FTP
 - 1 to 21 to 65535
- SNMP
 - 1 to 161 to 65535
- MTU Size
 - 1300, 1400, 1500

SNMP Settings

- SNMPv1 Settings
 - Off, On
- SNMPv3 Settings
 - Off, On
- Acquire Printer Management Information from Host
 - Off, On

Dedicated Port

- Off, On

Waiting Time for Connection at Startup

- 0 to 300 (sec.)

Ethernet Driver Settings

- MAC Address
- Auto Detect
 - Off, On
- Communication Mode
 - Half Duplex, Full Duplex
- Ethernet Type
 - 10BASE-T, 100BASE-TX

IEEE 802.1X Settings

- Off, On

Device Settings Management On/Off

- Off, On

Initialize Network Settings

Preferences

Display Settings

- Default Screen after Startup/Restoration
 - Home, Copy, Fax, Scan, Memory Media Print
- Home Screen Button Display Settings
 - Select Button to Display
 - Favorite Copy Settings
 - Favorite Fax Settings
 - Favorite Scan Settings
 - Set Display Order
 - Insert and Delete Blank
- Brightness
 - 5 Levels
- Invert Screen Colors
 - Off, On
- Millimeter/Inch Entry Switch
 - Millimeter, Inch
- Gram/Pound Switch
 - Gram, Pound
- Message Display Time
 - 1 to 2 to 5 (sec.)
- Scrolling Speed
 - Slow, Standard, Fast
- Cursor Movement Type
 - Auto, Manual
- Language
 - English, Japanese, French, Spanish, German, Italian, Portuguese, Chinese (Simplified), Chinese (Traditional), Korean
- Remote UI Language
 - English, Japanese, French, Spanish, German, Italian, Portuguese, Chinese (Simplified), Chinese (Traditional), Korean

English Keyboard Layout

- USA Layout, UK Layout

Timer Settings

Date/Time Settings

- Date Format
 - YYYY MM/DD, MM/DD/YYYY, DD/MM YYYY
- Time Format
 - 12 Hour (AM/PM), 24 Hour
- Current Date/Time Settings
- Time Zone
 - UTC-12:00 to (UTC-05:00) Eastern Time (US & Canada) to UTC+14:00
- Daylight Saving Time Settings
 - Off, On
- Start: Month, Week, Day
- End: Month, Week, Day

Auto Reset Time

- 0=Off (Auto Reset is disabled), 1 to 2 to 9 (min.)

Function After Auto Reset

- Default Function, Selected Function

Auto Sleep Time

- 10 to 240 (min.)

Auto Offline Time

- 0=Off (The machine remains online), 1 to 5 to 60 (min.)

Common Settings

Drawer Auto Selection On/Off

- Copy
 - Multi-Purpose Tray
 - Off, On
 - Drawer 1
 - Off, On
 - Drawer 2*
 - Off, On
- Printer
 - Drawer 1
 - Off, On
 - Drawer 2*
 - Off, On
- Fax
 - Multi-Purpose Tray
 - Off, On
 - Drawer 1
 - Off, On
 - Drawer 2*
 - Off, On
- Other
 - Multi-Purpose Tray
 - Off, On
 - Drawer 1
 - Off, On
 - Drawer 2*
 - Off, On

Switch Paper Feed Method

- Multi-Purpose Tray
 - Speed Priority, Print Side Priority
- Drawer 1
 - Speed Priority, Print Side Priority
- Drawer 2*
 - Speed Priority, Print Side Priority

Copy Settings

Change Default Settings

- Number of Copies
 - 1 to 999
- Density
 - 9 Levels
- Original Type
 - Text/Photo/Map (Speed), Text/Photo/Map (Quality), Printed Image, Text
- 2-Sided
 - Off, 1-Sided->2-Sided, 2-Sided->2-Sided, 2-Sided->1-Sided, Original/Finishing Type
- Copy Ratio
 - Custom Ratio, 100% (Direct), 400% (Max), 200%, 129% STMT->LTR, 78% LGL->LTR, 64% LTR->STMT, 50%, 25% (Min)
- Paper
 - Multi-Purpose Tray, Drawer 1, Drawer 2*, Auto Select Paper (LTR/LGL)
- N on 1
 - Off, 2 on 1, 4 on 1, ID Card Copy, Select Layout
- Collate
 - Off, On
- Erase Frame
 - Off, On
- Sharpness
 - 7 Levels
- Color Balance
 - Yellow
 - 17 Levels
 - Magenta
 - 17 Levels
 - Cyan
 - 17 Levels
 - Black
 - 17 Levels
 - Fine Adjust
 - Yellow
 - High: 17 Levels
 - Medium: 17 Levels
 - Low: 17 Levels
 - Magenta
 - High: 17 Levels
 - Medium: 17 Levels
 - Low: 17 Levels
 - Cyan
 - High: 17 Levels
 - Medium: 17 Levels
 - Low: 17 Levels
 - Black
 - High: 17 Levels
 - Medium: 17 Levels
 - Low: 17 Levels

Initialize Default Settings

Settings marked with an asterisk (*) are only available when the optional paper drawer (drawer 2) is attached.

Fax Settings

Basic Settings

- Register Unit Telephone Number
- Select Line Type
 - Pulse, Tone
- Off-Hook Alarm
 - 0 to 3
- Communication Management Settings
 - TX Start Speed
 - 33600 bps, 14400 bps, 9600 bps, 7200 bps, 4800 bps, 2400 bps
 - RX Start Speed
 - 33600 bps, 14400 bps, 9600 bps, 7200 bps, 4800 bps, 2400 bps
 - Archive TX Document
 - Off, On

TX Function Settings

- Change Default Setting
 - Resolution
 - 200 x 100 dpi (Normal), 200 x 200 dpi (Fine), 200 x 200 dpi (Photo), 200 x 400 dpi (Superfine), 400 x 400 dpi (Ultrafine)
 - Density
 - 9 Levels
 - 2-Sided Original
 - Off, Book Type, Calendar Type
 - Sharpness
 - 7 Levels
- Register Unit Name (Fax)
- ECM TX
 - Off, On
- Set Pause Time
 - 1 to 2 to 15 (sec.)
- Auto Redial
 - Off, On
 - Number of Times to Redial
 - 1 to 2 to 10 (times)
 - Redial Interval
 - 2 to 99 (min.)
 - Redial When Error Occurs
 - Off, On
- TX Terminal ID
 - Off, On
 - Print Position
 - Inside Image Area
 - Outside Image Area
 - Mark Number as: TEL/FAX
 - FAX, TEL
- Check Dial Tone Before Sending
 - Off, On
- Allow Fax Driver TX
 - Off, On
- Confirm Entered Fax Number
 - Off, On
- Restrict Sequential Broadcast
 - Off, Confirm Sequential Broadcast, Reject Sequential Broadcast
- Initialize Default Settings

RX Function Settings

- ECM RX
 - Off, On
- Incoming Ring
 - Off, On
 - 1 to 2 to 99 (times)
- Remote RX
 - Off, On
 - 00 to 25 to 99
- Switch to Auto RX
 - Off, On
 - 1 to 15 to 99 (sec.)
- Memory Lock Settings
 - Off, On
 - Memory Lock PIN
 - Report Print
 - Off, On
 - Memory Lock Time
 - Off, On
 - Memory Lock Start Time
 - Memory Lock End Time

RX Print Settings

- Print on Both Sides
 - Off, On
- Reduce RX Size
 - Off, On
 - Ratio
 - Auto, 97%, 95%, 90%, 75%
 - Direction
 - Vertical/Horizontal, Vertical Only
- RX Page Footer
 - Off, On
- Continue Printing When Amount in Cartridge Is Low
 - Off, On

Forwarding Settings

- Enable Forwarding Settings
 - Off, On
- Print Images
 - Off, On, Only When Error Occurs
- Store Images in Memory
 - Off, Only When Error Occurs

Fax Setup Guide

Settings marked with an asterisk (*) are only available when the optional paper drawer (drawer 2) is attached.

Menu Route Map

Scan Settings

USB Memory Settings

- Change Default Settings
 - Scan Size
 - LTR, LGL, STMT
 - File Format
 - PDF, PDF (Compact), PDF (Compact/OCR), PDF (OCR), JPEG, TIFF, Set PDF Details*1
 - Encryption Level
 - None
 - Acrobat 7.0 or Later/128-bit AES
 - Acrobat 9.0 or Equivalent/256-bit AES*2
 - Acrobat 10.0 or Equivalent/256-bit AES*2
 - Digital Signatures
 - None, Top Left
 - Density
 - 9 Levels
 - Original Orientation
 - Portrait, Landscape
 - Original Type
 - Text, Text/Photo, Photo
 - 2-Sided Original
 - Off, Book Type, Calendar Type
 - Sharpness
 - 7 Levels
 - Data Size
 - Small: Memory Priority, Standard, Large: Image Quality Priority
- Initialize Default Settings

E-Mail Settings

- Change Default Settings
 - Scan Size
 - LTR, LGL, STMT
 - File Format
 - PDF, PDF (Compact), PDF (Compact/OCR), PDF (OCR), JPEG, TIFF, Set PDF Details*1
 - Encryption Level
 - None
 - Acrobat 7.0 or Later/128-bit AES
 - Acrobat 9.0 or Equivalent/256-bit AES*2
 - Acrobat 10.0 or Equivalent/256-bit AES*2
 - Digital Signatures
 - None, Top Left
 - Density
 - 9 Levels
 - Original Orientation
 - Portrait, Landscape
 - Original Type
 - Text, Text/Photo, Photo
 - 2-Sided Original
 - Off, Book Type, Calendar Type
 - Sharpness
 - 7 Levels
 - Data Size
 - Small: Memory Priority, Standard, Large: Image Quality Priority
 - Subject/Message
 - Subject
 - Attached Image
 - Message
 - Reply To
 - None, Specify from Address Book
 - Priority
 - Low, Standard, High
- Initialize Default Settings

1-Fax Settings

TX Function Settings

- Change Default Settings
 - Scan Size
 - LTR, LGL, STMT
 - Density
 - 9 Levels
 - Original Type
 - Text, Text/Photo, Photo
 - 2-Sided Original
 - Off, Book Type, Calendar Type
 - Sharpness
 - 7 Levels
 - Subject/Message
 - Subject
 - Attached Image
 - Message
 - Reply To
 - None, Specify from Address Book
- TX Terminal ID
 - Off
 - On
 - Print Position
 - Inside Image Area, Outside Image Area
- Initialize Default Settings

RX Print Settings

- Print on Both Sides
 - Off, On
- RX Print Size
 - A4, LGL, LTR, OFICIO, Brazil-OFICIO, Mexico-OFICIO, Government-LTR, Government-LGL, FOOLSCAP, AUS-FOOLSCAP, India-LGL

File Settings

- Change Default Settings
 - Scan Size
 - LTR, LGL, STMT
 - File Format
 - PDF, PDF (Compact), PDF (Compact/OCR), PDF (OCR), JPEG, TIFF, Set PDF Details*1
 - Encryption Level
 - None
 - Acrobat 7.0 or Later/128-bit AES
 - Acrobat 9.0 or Equivalent/256-bit AES*2
 - Acrobat 10.0 or Equivalent/256-bit AES*2
 - Digital Signatures
 - None, Top Left
 - Density
 - 9 Levels
 - Original Orientation
 - Portrait, Landscape
 - Original Type
 - Text, Text/Photo, Photo
 - 2-Sided Original
 - Off, Book Type, Calendar Type
 - Sharpness
 - 7 Levels
 - Data Size
 - Small: Memory Priority, Standard, Large: Image Quality Priority
- Initialize Default Settings

Register Unit Name (E-Mail/1-Fax)

Output File Image Settings

- YCbCr TX Gamma Value
 - Gamma 1.0, Gamma 1.4, Gamma 1.8, Gamma 2.2
- PDF (Compact) Image Quality Level
 - Image Level In Text/Photo Mode or Photo Mode
 - Data Size Priority, Normal, Image Quality Priority
 - Image Level In Text Mode
 - Data Size Priority, Normal, Image Quality Priority

OCR (Text Searchable) Settings

- Smart Scan
 - Off, On

256-bit AES Settings for Encrypted PDF*1

- Acrobat 9.0 or Equivalent, Acrobat 10.0 or Equivalent

Settings marked with (*) are enabled only when an optional Send PDF Security Feature Set is registered.
Settings marked with (**) are available at a time, depending on the PDF encryption setting.

Memory Media Print Settings

Change Default Settings

- Number of Copies
 - 1 to 99
- Paper
 - Multi-Purpose Tray, Drawer 1, Drawer 2*
- Print on 1
 - Off, 2 on 1, 4 on 1
- 2-Sided Printing
 - Off, Book Type, Calendar Type
- Set JPEG/TIFF Details
 - Print Date
 - Off, On
 - Print File Name
 - Off, On
 - Original Type
 - Photo Priority, Text Priority
 - Brightness
 - 5 Levels
 - Halftones
 - Gradation, Error Diffusion
- Set PDF Details
 - Brightness
 - 7 Levels
 - Enlarge/Reduce to Fit Paper Size
 - Off, On
 - Enlarge Print Area
 - Off, On
 - Print Comments
 - Off, Auto
 - Password to Open Document
 - Other
 - Halftones
 - Error Diffusion
 - Off, On
 - Pure Black Text
 - Off, On
 - Black Overprint
 - Off, On
 - RGB Source Profile
 - sRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4, None
 - CMYK Simulation Profile
 - JapanColor(Canon), U.S. Web Coated v1.00(Canon), Euro Standard v1.00(Canon), None
 - Use Grayscale Profile
 - Off, On
 - Output Profile
 - Normal, Photo, TR Normal, TR Photo
 - Matching Method
 - Perceptual, Saturation, Colorimetric
 - RGB Pure Black Process
 - Off, On
 - CMYK Pure Black Process
 - Off, On
 - Composite Overprint
 - Off, On
 - Advanced Smoothing
 - Advanced Smoothing
 - Off, Smooth 1, Smooth 2
 - Apply to Graphics
 - Off, On
 - Apply to Text
 - Off, On
 - Grayscale Conversion
 - sRGB, NTSC, Uniform RGB
 - Print Quality
 - Density
 - Density: 17 levels
 - Fine Adjust
 - High: 17 levels
 - Medium: 17 levels
 - Low: 17 levels
 - Toner Save
 - Off, On
 - Special Smoothing Mode
 - Mode 1, Mode 2, Mode 3, Mode 4, Mode 5, Mode 6
 - Line Control
 - Resolution Priority, Gradation Priority

Default Display Settings

- Details, Images

File Sort Default Settings

- Name (Ascending), Name (Descending), Date/Time (Ascending), Date/Time (Descending)

File Name Display Format

- Short File Name, Long File Name

Initialize Default Set

Settings marked with an asterisk (*) are only available when the optional paper drawer (drawer 2) is attached.

Printer Settings

Prioritize Driver Settings When Printing

- Multi-Purpose Tray
 - Off, On
 - Force Output, Display Error
- Drawer 1
 - Off, On
 - Force Output, Display Error
- Drawer 2*1
 - Off, On
 - Force Output, Display Error

Copies*2

- 1 to 99 (Copies)

2-Sided Printing*2

- Off, On

Default Paper*2

- Default Paper Size
 - LTR, LGL, STMT, EXEC, No. 10 (COM10), Monarch, A4, A5, B5, DL, ISO-C5
- Default Paper Type
 - Plain 1 (16 lb Bond-19 lb Bond [60-74 g/m²]), Plain 2 (19 lb Bond-22 lb Bond [70-84 g/m²]), Plain 3 (20 lb Bond-23 lb Bond [75-90 g/m²]), Recycled, Color, Heavy 1 (23 lb Bond-31 lb Bond [86-119 g/m²]), Heavy 2 (32 lb Bond-34 lb Bond [120-128 g/m²]), Heavy 3 (35 lb Bond-60 lb Cover [129-163 g/m²]), Coated 1 (27 lb Bond-29 lb Bond [100-110 g/m²]), Coated 2 (32 lb Bond-34 lb Bond [120-130 g/m²]), Coated 3 (58 lb Cover-60 lb Cover [155-165 g/m²]), Coated 4 (78 lb Cover-81 lb Cover [210-220 g/m²]), Transparency, Labels, Envelope

Paper Size Override

- Off, On

Print Quality*2

- Density
 - Yellow
 - 17 Levels
 - Magenta
 - 17 Levels
 - Cyan
 - 17 Levels
 - Black
 - 17 Levels
- Density (Fine Adjust)
 - Yellow
 - High: 17 Levels
 - Medium: 17 Levels
 - Low: 17 Levels
 - Magenta
 - High: 17 Levels
 - Medium: 17 Levels
 - Low: 17 Levels
 - Cyan
 - High: 17 Levels
 - Medium: 17 Levels
 - Low: 17 Levels
 - Black
 - High: 17 Levels
 - Medium: 17 Levels
 - Low: 17 Levels
- Toner Save
 - Off, On
- Gradation
 - High 1, High 2
- Special Smoothing Mode
 - Mode 1, Mode 2, Mode 3, Mode 4, Mode 5, Mode 6
- Line Control
 - Resolution Priority, Gradation Priority

Layout*2

- Binding Location
 - Long Edge, Short Edge
- Gutter
 - 1.90 to ±0 to +1.90 (inches) or -50.0 to ±0 to +50.0 (mm)
- Offset Short Edge (Front)
 - 2.00 to ±0 to +2.00 (inches) or -50.0 to ±0 to +50.0 (mm)
- Offset Long Edge (Front)
 - 2.00 to ±0 to +2.00 (inches) or -50.0 to ±0 to +50.0 (mm)
- Offset Short Edge (Back)
 - 2.00 to ±0 to +2.00 (inches) or -50.0 to ±0 to +50.0 (mm)
- Offset Long Edge (Back)
 - 2.00 to ±0 to +2.00 (inches) or -50.0 to ±0 to +50.0 (mm)

Auto Error Skip*2

- Off, On

Timeout*2

- 5 to 15 to 300 (sec.)

Personality*2

- Auto, PS, PCL

Color Mode*2

- Auto (Color/B&W), Color, Black and White

Gradation Settings*2

- Gradation
 - Off, Smooth 1, Smooth 2
- Apply to Graphics
 - Off, On
- Apply to Images
 - Off, On

Compressed Image Output*2

- Output, Display Error

PCL*2

- Paper Save
 - Off, On
- Orientation
 - Portrait, Landscape
- Font Number
 - 0 to 104
- Point Size
 - 4.00 to 12.00 to 999.75 (point)
- Pitch
 - 0.44 to 10.00 to 99.99 (cpi)
- Form Lines
 - 5 to 60 to 128 (lines)
- Character Code
 - ARABIC8, DESKTOP, GREEK8, HEBREW7, HEBREW8, ISO4, ISO6, ISO11, ISO15, ISO17, ISO21, ISO60, ISO69, ISOCYR, ISOGRK, ISOHEB, ISOL1, ISOL2, ISOL5, ISOL6, LEGAL, MATH8, MCTEXT, MSPUBL, PC775, PC8, PC850, PC851, PC852, PC862, PC864, PC866, PC8DN, PC8GRK, PC8TK, PC1004, PIFONT, PSMATH, PSTEXT, ROMAN8, VNINLT, VNMATH, VNUS, WIN30, WINARB, WINBALT, WINCYR, WINGRK, WINL1, WINL2, WINL5
- Custom Paper
 - Off, On
- Unit of Measure
 - Millimeters, Inches
- X dimension
 - 3 1/16 to 8 7/16 (inches) or 77 to 215 (mm)
- Y dimension
 - 5 to 13 15/16 (inches) or 127 to 355 (mm)
- Append CR to LF
 - Yes, No
- Enlarge A4 Print Width
 - Off, On

Halftones

- Error Diffusion
 - Off, On
- Resolution/Gradation
 - Text
 - Resolution, Gradation
 - Graphics
 - Resolution, Gradation
 - Image
 - Resolution, Gradation

RGB Source Profile

- sRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4
- Graphics
 - sRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4
- Image
 - sRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4

Output Profile

- Text
 - Normal, Photo
- Graphics
 - Normal, Photo
- Image
 - Normal, Photo

Matching Method

- Text
 - Perceptual, Saturation, Colorimetric
- Graphics
 - Perceptual, Saturation, Colorimetric
- Image
 - Perceptual, Saturation, Colorimetric

Gray Compensation

- Text
 - Off, On
- Graphics
 - Off, On
- Image
 - Off, On

CMS (Matching) Selection

- Printer, Host

CMS (Matching)/Gamma

- Text
 - Gamma, CMS
- Graphics
 - Gamma, CMS
- Image
 - Gamma, CMS

Gamma Correction

- Text
 - 1.0, 1.4, 1.8, 2.2
- Graphics
 - 1.0, 1.4, 1.8, 2.2
- Image
 - 1.0, 1.4, 1.8, 2.2

Advanced Smoothing

- Advanced Smoothing
 - Off, Smooth 1, Smooth 2
- Apply to Graphics
 - Off, On
- Apply to Text
 - Off, On

BarDIMM*

- Enable, Disable

FreeScale


- Off, -, , #, \$, /, \, ? , (,) , |

PS*2


- Job Timeout
 - 0 to 3600 (sec.)
- Print PS Errors
 - Off, On
- Pure Black Text
 - Off, On
- Black Overprint
 - Off, On
- RGB Source Profile
 - sRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4, None
- CMYK Simulation Profile
 - JapanColor(Canon), U.S. Web Coated v1.00(Canon), Euro Standard v1.00(Canon), None
- Use Grayscale Profile
 - Off, On
- Output Profile
 - Normal, Photo, TR Normal, TR Photo
- Matching Method
 - Perceptual, Saturation, Colorimetric
- RGB Pure Black Process
 - Off, On
- CMYK Pure Black Process
 - Off, On
- Halftones
 - Error Diffusion
 - Off, On
 - Resolution/Gradation
 - Text
 - Resolution, Gradation
 - Graphics
 - Resolution, Gradation
 - Image
 - Resolution, Gradation
- Brightness
 - 85 to 100 to 115 (%)
- Composite Overprint
 - Off, On
- Advanced Smoothing
 - Advanced Smoothing
 - Off, Smooth 1, Smooth 2
 - Apply to Graphics
 - Off, On
 - Apply to Text
 - Off, On
- Grayscale Conversion
 - sRGB, NTSC, Uniform RGB

Settings marked with asterisk (*) are only available when the optional paper drawer (drawer 2) is attached.
Settings marked with (**) are only available for the MF729Cdw.

Menu Route Map



Settings marked with an asterisk (*) are only available when the optional paper drawer (drawer 2) is attached.



Settings marked with an asterisk (*) are only available for the MF729Cdw.