

Menu Route Map

Network Settings

- Select Wired/Wireless LAN
 - Wired LAN, Wireless LAN
- Wireless LAN Settings
 - WPS Push Button Mode
 - WPS PIN Code Mode
 - SSID Settings
 - Select Access Point
 - Enter Manually
 - Security Settings
 - None
 - WEP
 - Open System, Shared Key
 - WPA/WPA2-PSK
 - Auto, AES-CCMP
 - Power Save Mode
 - Off, On
 - Connection Information
 - MAC Address
 - Wireless LAN Status
 - Latest Error Information
 - Channel
 - SSID Settings
 - Security Settings
 - Power Save Mode
- Enable Direct Connection
 - Off, On
- TCP/IP Settings
 - IPv4 Settings
 - IP Address Settings
 - Auto Acquire
 - Select Protocol
 - Off, DHCP
 - Auto IP
 - Off, On
 - Manually Acquire
 - IP Address: 0.0.0.0
 - Subnet Mask: 0.0.0.0
 - Gateway Address: 0.0.0.0
 - Check Settings
 - Auto Acquire
 - IP Address
 - Subnet Mask
 - Gateway Address
 - PING Command
 - DNS Settings
 - DNS Server Settings
 - Primary DNS Server: 0.0.0.0
 - Secondary DNS Server: 0.0.0.0
 - DNS Host Name/Domain Name Settings
 - Host Name
 - Domain Name
 - DNS Dynamic Update Settings
 - Off, On
 - 0 to 24 to 48 (hr.)
 - mDNS Settings
 - Off, On
 - DHCP Option Settings
 - Acquire Host Name
 - Off, On
 - DNS Dynamic Update
 - Off, On
 - Acquire DNS Server Address
 - Off, On
 - Acquire Domain Name
 - Off, On
 - Acquire WINS Server Address
 - Off, On
 - Acquire SMTP Server Address
 - Off, On
 - Acquire POP Server Address
 - Off, On
 - IPv6 Settings
 - Use IPv6
 - Off, On, Check Settings
 - Link-Local Address
 - Prefix Length
 - Stateless Address Settings
 - Off, On, Check Settings
 - Stateless Address
 - Prefix Length
 - Use DHCPv6
 - Off, On, Check Settings
 - Stateful Address
 - Prefix Length
 - DNS Settings
 - DNS Host Name/Domain Name Settings (Use IPv4 Host/Domain)
 - Off, On
 - Host Name
 - Domain Name
 - DNS Dynamic Update Settings
 - Off, On
 - Register Manual Address
 - Off, On
 - Register Stateful Address
 - Off, On
 - Register Stateless Address
 - Off, On
 - DNS Dynamic Update Interval
 - 0 to 24 to 48 (hr.)
 - mDNS Settings
 - Off, On
 - DHCP Option Settings
 - Acquire DNS Server Address
 - Off, On
 - Acquire Domain Name
 - Off, On
 - WINS Settings
 - WINS Resolution
 - Off, On (WINS Server Address: 0.0.0.0)
 - LPD Settings
 - LPD Print Settings
 - Off, On
 - RX Timeout
 - 1 to 5 to 60 (min.)
 - RAW Settings
 - RAW Print Settings
 - Off, On
 - RX Timeout
 - 1 to 5 to 60 (min.)
 - WSD Settings
 - WSD Print Settings
 - Use WSD Print
 - Off, On
 - Use WSD Browsing
 - Off, On
 - WSD Scan Settings
 - Use WSD Scan
 - Off, On
 - Use Computer Scan
 - Off, On
 - Use Multicast Discovery
 - Off, On
 - Use FTP PASV Mode
 - Off, On
 - Use HTTP
 - Off, On

Port Number Settings

- LPD
 - 1 to 515 to 65535
- RAW
 - 1 to 9100 to 65535
- WSD Multicast Discovery
 - 1 to 3702 to 65535
- HTTP
 - 1 to 80 to 65535
- Multicast Discovery
 - 1 to 427 to 65535
- POP3
 - 1 to 110 to 65535
- SMTP
 - 1 to 25 to 65535
- FTP
 - 1 to 21 to 65535
- SNMP
 - 1 to 161 to 65535
- MTU Size
 - 1300, 1400, 1500

SNMP Settings

- SNMPv1 Settings
 - Off, On
- SNMPv3 Settings
 - Off, On
- Acquire Printer Management Information from Host
 - Off, On

Dedicated Port Settings

- Off, On

Waiting Time for Connection at Startup

- 0 to 300 (sec.)

Ethernet Driver Settings

- MAC Address
- Auto Detect
 - Off, On
 - Communication Mode
 - Half Duplex, Full Duplex
 - Ethernet Type
 - 10BASE-T, 100BASE-TX, 1000BASE-T

IEEE 802.1X Settings

- Off, On

Device Settings Management On/Off

- Off, On

Initialize Network Settings

Preferences

Display Settings

- Default Screen after Startup/Restoration
 - Home, Copy, Fax, Scan, Memory Media Print
- Home Screen Button Display Settings
 - Select Button to Display
 - Favorite Copy Settings
 - Favorite Fax Settings
 - Favorite Scan Settings
 - Set Display Order
 - Insert and Delete Blank
- Brightness
 - Five Levels
- Invert Screen Colors
 - Off, On
- Millimeter/Inch Entry Switch
 - Millimeter, Inch
- Gram/Pound Switch
 - Gram, Pound
- Message Display Time
 - 1 to 2 to 5 (sec.)
- Scrolling Speed
 - Slow, Standard, Fast
- Cursor Movement Type
 - Auto, Manual
- Language
 - English, Japanese, French, Spanish, German, Italian, Portuguese, Chinese (Simplified), Chinese (Traditional), Korean
- Remote UI Language
 - English, Japanese, French, Spanish, German, Italian, Portuguese, Chinese (Simplified), Chinese (Traditional), Korean

English Keyboard Layout

- USA Layout, UK Layout

Timer Settings

Date/Time Settings

- Date Format
 - YYYY MM/DD, MM/DD/YYYY, DD/MM YYYY
- Time Format
 - 12 Hour (AM/PM), 24 Hour
- Current Date/Time Settings
 - Time Zone
 - UTC-12:00 to (UTC-05:00) Eastern Time (US & Canada) to UTC+14:00
 - Daylight Saving Time Settings
 - Off, On
 - Start: Month, Week, Day
 - End: Month, Week, Day
- Auto Reset Time
 - 0=Off (Auto Reset is disabled.), 1 to 2 to 9 (min.)
- Function After Auto Reset
 - Default Function, Selected Function
- Auto Sleep Time
 - 3 to 240 (min.)
- Auto Offline Time
 - 0=Off (The machine remains online.), 1 to 5 to 60 (min.)

Common Settings

Drawer Auto Selection On/Off

- Copy
 - Multi-Purpose Tray
 - Off, On
 - Drawer 1
 - Off, On
 - Drawer 2*
 - Off, On
- Printer
 - Drawer 1
 - Off, On
 - Drawer 2*
 - Off, On
- Receive/Fax
 - Multi-Purpose Tray
 - Off, On
 - Drawer 1
 - Off, On
 - Drawer 2*
 - Off, On
- Other
 - Multi-Purpose Tray
 - Off, On
 - Drawer 1
 - Off, On
 - Drawer 2*
 - Off, On

Switch Paper Feed Method

- Multi-Purpose Tray
 - Speed Priority, Print Side Priority
- Drawer 1
 - Speed Priority, Print Side Priority
- Drawer 2*
 - Speed Priority, Print Side Priority

Settings marked with (*) are only available when the optional paper drawer (drawer 2) is attached.

Copy Settings

Change Default Settings

- Number of Copies
 - 1 to 999
- Density
 - Nine Levels
 - Background
 - Auto
 - Adjust (Manual)
 - Nine Levels
- Original Type
 - Text, Text/Photo, Text/Photo (Quality), Photo
- 2-Sided
 - Off, 1-Sided->2-Sided, 2-Sided->2-Sided, 2-Sided->1-Sided, Original/Finishing Type
- Copy Ratio
 - Custom Ratio, 100% (Direct), 400% (Max), 200%, 129% STMT->LTR, 78% LGL->LTR, 64% LTR->STMT, 50%, 25% (Min)
- Paper
 - Multi-Purpose Tray, Drawer 1, Drawer 2*, Auto Select Paper (LTR/LGL)
- N on 1
 - Off, 2 on 1, 4 on 1, ID Card Copy, Select Layout
- Collate
 - Off, On
- Erase Frame
 - Off, On
- Sharpness
 - Seven Levels

Initialize Default Settings

Settings marked with (*) are only available when the optional paper drawer (drawer 2) is attached.

Fax Settings

Basic Settings

- Register Unit Telephone Number
- Select Line Type
 - Pulse, Tone
- Off-Hook Alarm
 - 0 to 3
- Communication Management Settings
 - TX Start Speed
 - 33600 bps, 14400 bps, 9600 bps, 7200 bps, 4800 bps, 2400 bps
 - RX Start Speed
 - 33600 bps, 14400 bps, 9600 bps, 7200 bps, 4800 bps, 2400 bps
 - Archive TX Document
 - Off, On

TX Function Settings

- Change Default Setting
 - Resolution
 - 200 x 100 dpi (Normal), 200 x 200 dpi (Fine), 200 x 200 dpi (Photo), 200 x 400 dpi (Superfine), 400 x 400 dpi (Ultrafine)
 - Density
 - Nine Levels
 - 2-Sided Original
 - Off, Book Type, Calendar Type
 - Sharpness
 - Seven Levels
- Register Unit Name (Fax)
- ECM TX
 - Off, On
- Set Pause Time
 - 1 to 2 to 15 (sec.)
- Auto Redial
 - Off, On
 - Number of Times to Redial
 - 1 to 2 to 10 (times)
 - Redial Interval
 - 2 to 99 (min.)
 - Redial When Error Occurs
 - Off, On
- TX Terminal ID
 - Off, On
 - Print Position
 - Inside Image Area, Outside Image Area
 - Mark Number as
 - FAX, TEL
- Check Dial Tone Before Sending
 - Off, On
- Allow Fax Driver TX
 - Off, On
- Confirm Entered Fax Number
 - Off, On
- Restrict Sequential Broadcast
 - Off, Confirm Sequential Broadcast, Reject Sequential Broadcast
- Initialize Default Settings

RX Function Settings

- ECM RX
 - Off, On
- Incoming Ring
 - Off, On
 - 1 to 2 to 99 (times)
- Remote RX
 - Off, On
 - 00 to 25 to 99
- Switch to Auto RX
 - Off, On
 - 1 to 15 to 99 (sec.)
- Memory Lock Settings
 - Off, On
 - Memory Lock PIN
 - Report Print
 - Off, On
 - Memory Lock Time
 - Off, On
 - Memory Lock Start Time
 - Memory Lock End Time

RX Print Settings

- Print on Both Sides
 - Off, On
- Reduce RX Size
 - Off, On
 - Ratio
 - Auto, 97%, 95%, 90%, 75%
 - Direction
 - Vertical/Horizontal, Vertical Only
- RX Page Footer
 - Off, On
- Continue Printing When Amount in Cartridge Is Low
 - Off, On

Forwarding Settings

- Enable Forwarding Settings
 - Off, On
- Print Images
 - Off, On, Only When Error Occurs
- Store Images in Memory
 - Off, Only When Error Occurs

Fax Setup Guide

Scan Settings

USB Memory Settings

- Change Default Settings
 - Scan Size
 - LTR, LGL, STMT
 - Color Mode
 - Color, Black & White
 - File Format
 - PDF, PDF (Compact), PDF (Compact/OCR), PDF (OCR), JPEG, TIFF
 - Density
 - Nine Levels
 - Original Orientation
 - Portrait, Landscape
 - Original Type
 - Text, Text/Photo, Photo
 - 2-Sided Original
 - Off, Book Type, Calendar Type
 - Sharpness
 - Seven Levels
 - Data Size
 - Small: Memory Priority, Standard, Large: Image Quality Priority
- Initialize Default Settings

E-Mail Settings

- Change Default Settings
 - Scan Size
 - LTR, LGL, STMT
 - Color Mode
 - Color, Black & White
 - File Format
 - PDF, PDF (Compact), PDF (Compact/OCR), PDF (OCR), JPEG, TIFF
 - Density
 - Nine Levels
 - Original Orientation
 - Portrait, Landscape
 - Original Type
 - Text, Text/Photo, Photo
 - 2-Sided Original
 - Off, Book Type, Calendar Type
 - Sharpness
 - Seven Levels
 - Data Size
 - Small: Memory Priority, Standard, Large: Image Quality Priority
 - Subject/Message
 - Subject
 - Message
 - Reply To
 - None, Specify from Address Book
 - Priority
 - Low, Standard, High
- Initialize Default Settings

I-Fax Settings

TX Function Settings

- Change Default Settings
 - Scan Size
 - LTR, LGL, STMT
 - Density
 - Nine Levels
 - Original Type
 - Text, Text/Photo, Photo
 - 2-Sided Original
 - Off, Book Type, Calendar Type
 - Sharpness
 - Seven Levels
 - Subject/Message
 - Subject
 - Message
 - Reply To
 - None, Specify from Address Book
- TX Terminal ID
 - Off, On
 - Print Position
 - Inside Image Area, Outside Image Area
- Initialize Default Settings

RX Print Settings

- Print on Both Sides
 - Off, On
- RX Print Size
 - A4, LGL, LTR, OFICIO, Brazil-OFICIO, Mexico-OFICIO, Government-LTR, Government-LGL, FOOLSCAP, AUS-FOOLSCAP, India-LGL

File Settings

- Change Default Settings
 - Scan Size
 - LTR, LGL, STMT
 - Color Mode
 - Color, Black & White
 - File Format
 - PDF, PDF (Compact), PDF (Compact/OCR), PDF (OCR), JPEG, TIFF
 - Density
 - Nine Levels
 - Original Orientation
 - Portrait, Landscape
 - Original Type
 - Text, Text/Photo, Photo
 - 2-Sided Original
 - Off, Book Type, Calendar Type
 - Sharpness
 - Seven Levels
 - Data Size
 - Small: Memory Priority, Standard, Large: Image Quality Priority
- Initialize Default Settings

Register Unit Name (E-Mail/I-Fax)

Output File Image Settings

- YCbCr TX Gamma Value
 - Gamma 1.0, Gamma 1.4, Gamma 1.8, Gamma 2.2

OCR (Text Searchable) Settings

- Smart Scan
 - Off, On

Menu Route Map

Memory Media Print Settings

- Change Default Settings**
 - Number of Copies: 1 to 99
 - Paper: Multi-Purpose Tray, **Drawer 1**, Drawer 2*
 - N on 1: **Off**, 2 on 1, 4 on 1
 - 2-Sided Printing: **Off**, Book Type, Calendar Type
 - Print Quality
 - Density: 17 Levels, Density (Fine Adjust), High: 17 Levels, Medium: 17 Levels, Low: 17 Levels
 - Toner Save: **Off**, On
 - Set JPEG/TIFF Details
 - Print Date: **Off**, On
 - Print File Name: **Off**, On
 - Original Type: **Photo Priority**, Text Priority
 - Brightness: Five Levels
 - Halftones: Gradation, **Error Diffusion**
 - Grayscale Conversion: sRGB, **NTSC**, Uniform RGB
 - Set PDF Details
 - Enlarge/Reduce to Fit Paper Size: **Off**, On
 - Enlarge Print Area: **Off**, On
 - Print Comments: **Off**, **Auto**
 - Other
 - Halftones: Text: **Resolution**, Gradation, High Resolution; Graphics: **Resolution**, Gradation, High Resolution; Image: **Resolution**, Gradation, High Resolution; Grayscale Conversion: sRGB, **NTSC**, Uniform RGB
- Default Display Settings**: **Details**, Images
- File Sort Default Settings**: **Name (Ascending)**, Name (Descending), Date/Time (Ascending), Date/Time (Descending)
- File Name Display Format**: Short File Name, **Long File Name**
- Initialize Default Settings**

Settings marked with (*) are only available when the optional paper drawer (drawer 2) is attached.

Printer Settings

- Prioritize Driver Settings When Printing**
 - Multi-Purpose Tray: **Off**, On
 - Drawer 1: **Off**, On, **Force Output**, Display Error
 - Drawer 2*1: **Off**, On, **Force Output**, Display Error
- Copies**: 1 to 99
- 2-Sided Printing**: **Off**, On
- Default Paper**
- Paper Size Override**: **Off**, On
- Print Quality**
 - Density: 17 Levels, Fine Adjust, High: 17 Levels, Medium: 17 Levels, Low: 17 Levels
 - Toner Save: **Off**, On
 - Resolution: 1200 dpi, **600 dpi**
 - Barcode Adjustment Mode: **Off**, Mode 1, Mode 2, Mode 3
- Layout**
 - Binding Location: **Long Edge**, Short Edge
 - Gutter: -1.90 to **0.00** to +1.90 (inches) or -50.0 to **00.0** to +50.0 (mm)
 - Offset Short Edge (Front): -2.00 to **0.00** to +2.00 (inches) or -50.0 to **00.0** to +50.0 (mm)
 - Offset Long Edge (Front): -2.00 to **0.00** to +2.00 (inches) or -50.0 to **00.0** to +50.0 (mm)
 - Offset Short Edge (Back): -2.00 to **0.00** to +2.00 (inches) or -50.0 to **00.0** to +50.0 (mm)
 - Offset Long Edge (Back): -2.00 to **0.00** to +2.00 (inches) or -50.0 to **00.0** to +50.0 (mm)
- Auto Error Skip**: **Off**, On
- Timeout**: 5 to **15** to 300 (sec.)
- Personality**: **Auto**, PS, PCL, PDF, XPS
- UFR II**
 - Halftones: Text: **Resolution**, Color Tone, Gradation, High Resolution; Graphics: **Resolution**, **Color Tone**, Gradation, High Resolution; Images: **Resolution**, **Color Tone**, Gradation, High Resolution

PCL

- Paper Save: **Off**, On
- Orientation: **Portrait**, Landscape
- Font Number: 0 to 104 (MF419dw) / 0 to 54 (MF416dw / MF414dw)
- Point Size: 4.00 to **12.00** to 999.75 (point)
- Pitch: 0.44 to **10.00** to 99.99 (dpi)
- Form Lines: 5 to **60** to 128 (lines)
- Character Code: ARABIC8*2, DESKTOP, GREEK8*2, HEBREW7*2, HEBREW8*2, ISO4, ISO6, ISO11, ISO15, ISO17, ISO21, ISO60, ISO69, ISOCR*2, ISOCR*2, ISOHEB*2, ISOL1, ISOL2, ISOL5, ISOL6, LEGAL, MATH8, MCTEXT, MSPUBL, PC775, **PC8**, PC850, PC851, PC852*2, PC862*2, PC864*2, PC866*2, PC8DN, PC8GRK*2, PC8TK, PC1004, PIFONT, PSMATH, PSTEXT, ROMAN8, VNINTL, VNMATH, VNUS, WIN30, WINARB*2, WINBALT, WINGYR*2, WINGRK*2, WINL1, WINL2, WINL5
- Custom Paper: **Off**, On
- Unit of Measure: Millimeters, **Inches**
- X dimension: 3 to **8 1/2** (inches) or 77 to **216** (mm)
- Y dimension: 5 to **14** (inches) or 127 to **356** (mm)
- Append CR to LF: Yes, **No**
- Enlarge A4 Print Width: **Off**, On
- Halftones: Text: **Resolution**, Color Tone, Gradation, High Resolution; Graphics: **Resolution**, **Color Tone**, Gradation, High Resolution; Images: **Resolution**, **Color Tone**, Gradation, High Resolution
- BarDIMM*2: Enable, **Disable**
- FreeScale: **Off**, ~, *, #, \$, /, \, ?, {, }, |

PS*3

- Job Timeout: 0 to 3600 (sec.)
- Print PS Errors: **Off**, On
- Halftones: Text: **Resolution**, Gradation, High Resolution; Graphics: **Resolution**, Gradation, High Resolution; Images: **Resolution**, Gradation, High Resolution
- Grayscale Conversion: sRGB, **NTSC**, Uniform RGB

PDF

- Enlarge/Reduce to Fit Paper Size: **Off**, On
- Enlarge Print Area: **Off**, On
- N on 1: **Off**, 2 on 1, 4 on 1, 6 on 1, 8 on 1, 9 on 1, 16 on 1
- Print Comments: **Off**, **Auto**
- Halftones: Text: **Resolution**, Gradation, High Resolution; Graphics: **Resolution**, Gradation, High Resolution; Images: **Resolution**, Gradation, High Resolution
- Grayscale Conversion: sRGB, **NTSC**, Uniform RGB

XPS

- Halftones: Text: **Resolution**, Gradation, High Resolution; Graphics: **Resolution**, Gradation, High Resolution; Images: **Resolution**, Gradation, High Resolution
- Grayscale Conversion: Text: sRGB, **NTSC**, Uniform RGB; Graphics: sRGB, **NTSC**, Uniform RGB; Images: sRGB, **NTSC**, Uniform RGB
- Compressed Image Output: **Output**, Display Error

Settings marked with (*1) are only available when the optional paper drawer (drawer 2) is attached.
Settings marked with (*2) are only available for the MF419dw.
Settings marked with (*3) are only available for the MF419dw / MF416dw.

Adjustment/Maintenance

- Adjust Copy Image**
- Display Timing for Cartridge Preparation Notification**: **Auto**, Custom
- Printer Density**: Nine Levels
- Toner Save**: **Off**, On
- Special Processing**
 - Special Printing Mode A: **Off**, **Mode 1**, Mode 2, Mode 3, Mode 4
 - Special Printing Mode U: **Off**, On
 - Special Printing Mode V: **Off**, Mode 1, Mode 2
 - Special Printing Mode Z: **Off**, **Mode 1**, Mode 2, Mode 3
 - Special Printing Mode B: **Off**, Mode 1, Mode 2, Mode 3
 - Special Printing Mode C: **Off**, On
 - Special Printing Mode D: **Off**, On
- Clean Fixing Assembly**
- Clean Feeder**

System Management Settings

- Network Settings**: -> Network Settings
- Enable NFC*1**: **Off**, **On**
- System Manager Information Settings**
 - System Manager ID and PIN
 - System Manager ID
 - System Manager PIN
 - System Manager Name
- Device Information Settings**
 - Device Name
 - Location
- Department ID Management On/Off**: **Off**, On
- Security Settings**
 - Use TLS: **Off**, On
 - Use IPsec: **Off**, On
 - IPv4 Address Filter: Outbound Filter: **Off**, On; Inbound Filter: **Off**, On
 - IPv6 Address Filter: Outbound Filter: **Off**, On; Inbound Filter: **Off**, On
 - MAC Address Filter: Outbound Filter: **Off**, On; Inbound Filter: **Off**, On
- Select Country/Region**: **United States (US)**, Canada (CA), Brazil (BR), Mexico (MX), Other
- Remote UI Settings**
 - Use Remote UI: **Off**, **On**
 - Remote UI Access Security Settings: **Off**, On
 - Remote UI Access PIN
- Auto Online for Remote Scan**: **Off**, **On**
- Restrict TX Function**
 - Address Book PIN
 - Restrict New Destinations: **Off**, On
 - Restrict Resending from Log: **Off**, On
 - Coded Dial TX Confirmation: **Off**, On
- Display Job Log**: **Off**, **On**
- Use as USB Device**: **Off**, **On**
- Store to USB Memory**: **Off**, On (MF419dw) / **Off**, **On** (MF416dw / MF414dw)
- Memory Media Print On/Off**: **Off**, On (MF419dw) / **Off**, **On** (MF416dw / MF414dw)
- Enable Product Extended Survey Program**: **Off**, **On**
- Display Consumables Information (RUI/Toner Status)**
 - Display Consumables Purchase Button (RUI): **Off**, **On**
 - Toner Status Settings: **Off**, **On** (Consumbls. Purchase Btn.)
- Enable Canon Mobile Scanning**: **Off**, **On**
- Google Cloud Print Settings**
 - Enable Google Cloud Print: **Off**, **On**
 - Google Cloud Print Registration Status
- Notify to Check Paper Settings**: **Off**, **On**
- Import/Export of Settings**
 - Import
 - Export
- Secure Print Settings**: **Off**, **On** (Secure Print Deletion Time) 10 to **30** to 240 (min.)
- PDL Selection (Plug and Play)**
 - Network: Fax, **UFR II**, UFR II (V4), PCL6, PS*2
 - USB: Fax, **UFR II**, UFR II (V4), PCL6, PS*2
- Update Firmware**
 - Via PC
 - Via Internet
 - Version Information
- Register License*3**
- Initialize Key and Certificate**
- Initialize Address Book**
- Initialize Menu**
 - Preferences
 - Timer Settings
 - Common Settings
 - Copy Settings
 - Fax Settings
 - Scan Settings
 - Memory Media Print Settings
 - Printer Settings
 - System Management Settings
 - Network Settings
 - Enable NFC*1
 - System Manager Information Settings
 - Device Information Settings
 - Department ID Management On/Off
 - Security/Remote UI Settings
 - Auto Online for Remote Scan
 - Restrict TX Function
 - Register LDAP Server
 - Authentication Settings for Send Function
 - Display Job Log
 - Use as USB Device
 - Store to USB Memory
 - Memory Media Print On/Off
 - Enable Product Extended Survey Program
 - Information for Purchasing Consumables
 - Enable Canon Mobile Scanning
 - Google Cloud Print Settings
 - Notify to Check Paper Settings
 - Secure Print Settings
 - PDL Selection (Plug and Play)
 - Initialize All
- Initialize All Data/Settings**

Settings marked with (*1) are only available for the MF416dw.
Settings marked with (*2) are only available for the MF419dw / MF416dw.
Settings marked with (*3) are only available for the MF419dw.