

Menu Route Map

NOTE

- Red color values indicate the default settings.
- The setting items or setting values with "*" may not be displayed depending on the availability of the optional accessories and other settings.

See the e-Manual for details on settings.

[Setup] Menu

Control Menu

- Sleep Mode
 - High (Deep Sleep)
 - Mid (Printer Sleep)
 - Low (Panel Sleep)
 - Off
- Sleep Even if Error
 - Off
 - On
- Auto Sleep Time
 - 5 minutes
 - 10 minutes
 - 15 minutes
 - 30 minutes
 - 60 minutes
 - 180 minutes
- Timer Settings
 - Wake Up Timer
 - Off
 - On
 - Wake Up Time
 - 00:00 AM/PM to 12:00 PM to 11:59 AM/PM (00:00 to 12:00 to 23:59)
 - Auto Reset Time
 - Off
 - 10 seconds
 - 20 seconds
 - 30 seconds
 - 40 seconds
 - 50 seconds
 - 1 minute
 - 2 minutes
 - 3 minutes
 - 4 minutes
 - 5 minutes
 - 6 minutes
 - 7 minutes
 - 8 minutes
 - 9 minutes
 - Sleep Mode Timer
 - Off
 - On
 - Sleep Mode Time
 - 00:00 AM/PM to 12:00 PM to 11:59 AM/PM (00:00 to 12:00 to 23:59)
- Warning Step
 - Toner Cart. Warning
 - Continue Printing
 - Stop Printing
- Auto Continue
 - Off
 - On
- Panel Language
 - Deutsch
 - English
 - Español
 - Français
 - Italiano
 - 中文 (简体)
 - 한국어
- Alarm
 - Off
 - On
- Show Warnings
 - Toner Cart. Warning
 - Off
 - On
 - Drawer Empty
 - Off
 - On
 - E-Mail Trans. Error
 - Off
 - On

- Date/Time Settings
 - Date
 - 01/01/2001 to 31/12/2030
 - 12/24 Hour Clock
 - AM/PM
 - 24 Hour
 - Time
 - 00:00:00 AM/PM to 11:59:59 AM/PM (00:00:00 to 23:59:59)
 - Daylight Savings*
 - DST Settings: Off, On
 - Start Date/Time: Month, Week, Day, Time
 - End Date/Time: Month, Week, Day, Time
 - Time Zone*
 - GMT-12:00 to GMT+12:00
- SD Card*
 - Off
 - On
- Interrupt Print*
 - Off
 - On
- Sec. Print Del. Time*
 - 1 hour
 - 2 hours
 - 3 hours
 - 6 hours
 - 12 hours
 - 24 hours
- Secure Job Log*
 - Off
 - On
- Select PDL (PnP)
 - UFR II
 - UFR II XPS
 - PCL5e
 - PCL6
 - PS3
 - XPS (Direct)
- Mng. Settings
 - Settings Key Lock
 - Off
 - On
- Adjust Screen
 - Contrast
 - 3 Dark to 0 to +3 Light
 - Backlight Brightness
 - Off
 - Level 1
 - Level 2
 - Level 3
- Animated Instruction
 - Off
 - On
- Show Toner Gauge
 - Off
 - On
- Set. Comp. Notify
 - Off
 - 1 second
 - 2 seconds
 - 3 seconds
- Scrolling Speed
 - Slow
 - Normal
 - Fast

Paper Source

- Paper Source
 - Auto
 - Drawer 1
 - Drawer 2*
 - Drawer 3*
 - Multi-Purpose Tray

- MP Tray Paper Size
 - A6
 - A5
 - A5R
 - B5
 - A4
 - LTR
 - LGL
 - EXEC
 - Mixed Sizes
 - Custom Size
 - Custom Size R
 - Env. ISO-C5
 - Env. Monarch
 - Env. No.10
 - Env. DL
 - Index Card
 - STMT
 - FLSC
 - 16K
- MP Tray Priority
 - Off
 - On
- Drawer 1 Size
 - A6
 - A5
 - A5R
 - B5
 - A4
 - LTR
 - LGL
 - EXEC
 - Mixed Sizes
 - Custom Size
 - Custom Size R
 - STMT
 - FLSC
 - 16K
- Drawer 2 Size*
 - A6
 - A5
 - A5R
 - B5
 - A4
 - LTR
 - LGL
 - EXEC
 - Mixed Sizes
 - Custom Size
 - Custom Size R
 - STMT
 - FLSC
 - 16K
- Drawer 3 Size*
 - A6
 - A5
 - A5R
 - B5
 - A4
 - LTR
 - LGL
 - EXEC
 - Mixed Sizes
 - Custom Size
 - Custom Size R
 - STMT
 - FLSC
 - 16K
- Standard Paper Size
 - A6
 - A5
 - B5
 - A4
 - LTR
 - LGL

- EXEC
- Env. ISO-C5
- Env. Monarch
- Env. No.10
- Env. DL
- Index Card
- STMT
- FLSC
- 16K
- Diff. Paper Tray
 - Off
 - On
- Auto Selection
 - Multi-Purpose Tray
 - Off
 - On
 - Drawer 1
 - Off
 - On
 - Drawer 2*
 - Off
 - On
 - Drawer 3*
 - Off
 - On
- Default Paper Type
 - Plain
 - Plain L
 - Heavy 1
 - Heavy 2
 - Transparency
 - Envelope
 - Labels
- 2-Sided Printing
 - Off
 - On

Network

TCP/IP Settings

- IPv4 Settings
 - IPv4: Off, **On**
 - IP Mode: **Auto**, Manual
 - Protocol*
 - Use DHCP: Off, **On**
 - Use BOOTP: **Off**, On
 - Use RARP: **Off**, On
 - IP Address Settings
 - IP Address: 0.0.0.0
 - Subnet Mask: 0.0.0.0
 - Gateway Address: 0.0.0.0
 - DNS
 - Primary Address: 0.0.0.0
 - Secondary Address: 0.0.0.0
 - DHCP Option
 - Acquire Host Name: Off, **On**
 - DNS Dynamic Update: **Off**, On
- IPv6 Settings
 - IPv6: **Off**, On
- WINS Resolution
 - Off
 - On
- ARP/PING
 - Off
 - On
- FTP
 - FTP Print: **Off**, On
 - FTP Settings: **Off**, On
- LPD Print
 - Off
 - On
- RAW Print
 - Off
 - On
- IPP Print
 - Off
 - On
- WSD
 - WSD Print: **Off**, On
 - WSD Browsing*: **Off**, On
 - Multicast Discovery: **Off**, On

- HTTP
 - Off
 - On**
- Proxy Settings
 - Proxy: **Off**, On
 - Server Address*
 - Port Number*: 1 to **80** to 65535
 - Same Domain*: Use Proxy, **Do Not Use Proxy**
 - Proxy Authentication*: **Off**, On
 - User Name*
 - Password*
- SNTP
 - Off
 - On
- Discovery Response
 - Off
 - On
- IPSec
 - Off
 - On
- NetWare Settings
 - NetWare
 - Off
 - On
 - Frame Type*
 - Auto Detect**
 - Ethernet II
 - Ethernet 802.2
 - Ethernet 802.3
 - Ethernet SNAP
 - Print Service*
 - Bindery PServer
 - RPrinter
 - NDS PServer**
 - NPrinter
- AppleTalk
 - Off
 - On
- SMB*
 - SMB Server
 - Off
 - On
 - SMB Print*
 - Off
 - On
- SNMP v. 1 Settings
 - SNMP v. 1
 - Off
 - On**
 - Dctd. Community Set.
 - Dctd. Community: Off, Read/Write, **Read Only**
- SNMP v. 3 Settings
 - SNMP v. 3
 - Off
 - On
 - User Settings 1 to User Settings 5*
 - Auth. Password
 - Encryption Password
- Spooler*
 - Off
 - On
- Network Delay Time
 - 0 to 300 seconds
- Remote UI Settings
 - Remote UI
 - Off
 - On**
 - SSL*
 - Off
 - On
- Ethernet Driver
 - Auto Detect
 - Off
 - On**
 - Communication Mode*
 - Half Duplex**
 - Full Duplex
 - Ethernet Type*
 - 10 Base-T**
 - 100 Base-TX
 - 1000 Base-T

- IEEE802.1X
 - Off
 - On
- Address Filter
 - Off
 - On**
- MAC Address
 - (Display only)
- E-Mail Print Set.
 - POP3 RX Interval
 - 0 to 90 (minutes)
 - POP3 RX
 - Off
 - On
 - SMTP RX
 - Off
 - On
- Init. Network Set.

Layout

- Copies
 - 1 to 9999
- Offset Y
 - 1.97 to **0.00** to +1.97 (in.)
- Offset X
 - 1.97 to **0.00** to +1.97 (in.)
- Binding Location
 - Long Edge**
 - Short Edge
- Gutter
 - 1.97 to **0.00** to +1.97 (in.)
- Alternative Method
 - Off
 - On**

Quality

- Resolution
 - 600 dpi**
 - 1200 dpi
- Image Refinement*
 - Off
 - On**
- Toner Save
 - Off
 - On
- Density*
 - 8 Light to **0** to +8 Dark
- Density (Fine Adj)*
 - High
 - 8 Light to **0** to +8 Dark
 - Mid
 - 8 Light to **0** to +8 Dark
 - Low
 - 8 Light to **0** to +8 Dark
- Halftones
 - Text
 - Resolution**
 - Gradation
 - Color Tone
 - High Resolution
 - Graphics
 - Resolution
 - Gradation
 - Color Tone**
 - High Resolution
 - Image
 - Resolution
 - Gradation
 - Color Tone**
 - High Resolution
- Reduce Quality
 - Continue Printing**
 - Stop Printing

Interface

- Interface Selection
 - USB
 - Off
 - On**
 - Network
 - Off
 - On**

Timeout

- Timeout
 - Off
 - On**
- Timeout Time*
 - 5 to **15** to 300 seconds

Connection Recog.

- Off
- On**

Extended RX Buffer

- Off**
- On

User Maintenance

Adj. Start Position

- Offset Y (MP Tray)
 - 0.20 to **0.00** to +0.20 (in.)
- Offset X (MP Tray)
 - 0.20 to **0.00** to +0.20 (in.)
- Offset Y (Drawer 1)
 - 0.20 to **0.00** to +0.20 (in.)
- Offset X (Drawer 1)
 - 0.20 to **0.00** to +0.20 (in.)
- Offset Y (Drawer 2)*
 - 0.20 to **0.00** to +0.20 (in.)
- Offset X (Drawer 2)*
 - 0.20 to **0.00** to +0.20 (in.)
- Offset Y (Drawer 3)*
 - 0.20 to **0.00** to +0.20 (in.)
- Offset X (Drawer 3)*
 - 0.20 to **0.00** to +0.20 (in.)
- Offset Y (2-Sided)
 - 0.20 to **0.00** to +0.20 (in.)
- Offset X (2-Sided)
 - 0.20 to **0.00** to +0.20 (in.)

Recovery Printing

- Off
- On**

Check Paper Size

- Off**
- On

Substitute Size

- Off**
- On

Special Print Mode A

- Off
- Mode 1**
- Mode 2
- Mode 3
- Mode 4

SD Card Maintenance*

- Format

Special Print Mode

- Curl Correction
 - Multi-Purpose Tray: **Off**, On
 - Drawer 1: **Off**, On
 - Drawer 2*: **Off**, On
 - Drawer 3*: **Off**, On
- Plain L Speed Prior.
 - Off**
 - On

Special Print Adj. C

- Off**
- On

Special Print Adj. D

- Off**
- On

Update Firmware

- USB
- Network

Paper Feed Method

- Multi-Purpose Tray
 - Speed Priority**
 - Print Side Priority
- Drawer 1
 - Speed Priority**
 - Print Side Priority
- Drawer 2*
 - Speed Priority**
 - Print Side Priority

- Drawer 3*
 - Speed Priority**
 - Print Side Priority
- Show Job List
 - Off
 - On**
- IMPORT/EXPORT
 - EXPORT
 - IMPORT

Print Mode

Auto Mode Selection

- Auto Selection**
- PCL
- PS
- PDF
- XPS

Auto Select

- PCL
 - Off
 - On**
- PS
 - Off
 - On**
- PDF
 - Off
 - On**
- XPS
 - Off
 - On**

Mode Priority

- None**
- PCL
- PS
- PDF
- XPS

UFR II

- Paper Save
 - Off
 - On**












PCL

- Paper Save
 - Off**
 - On
- Orientation
 - Portrait**
 - Landscape
- Font Number
 - 0** to 104
- Point Size*
 - 4.00 to **12.00** to 999.75 point
- Pitch*
 - 0.44 to **10.00** to 99.99 cpi
- Form Lines
 - 5 to **60** to 128 lines
- Character Code
 - PC8**
 - ROMAN8
 - ROMAN9
 - ISOL1
 - ISOL2
 - ISOL5
 - ISOL6
 - ISOL9
 - PC775
 - PC8DN
 - PC850
 - PC852
 - PC858
 - PC8TK
 - PC1004
 - WINL1
 - WINL2
 - WINL5
 - WINBALT
 - DESKTOP
 - PSTEXT
 - LEGAL
 - ISO4
 - ISO6

- ISO11
- ISO15
- ISO17
- ISO21
- ISO60
- ISO69
- WIN 30
- MCTEXT
- PC864
- ARABIC8
- WINARB
- PC866
- ISOCYR
- WINCYR
- PC851
- GREEK8
- ISOGRK
- PC8GRK
- WINGRK
- PC862
- HEBREW7
- HEBREW8
- ISOHEB
- Custom Size
 - Do Not Set**
 - Set
- Unit of Measurement*
 - Millimeters
 - Inches**
- X Dimension*
 - 3.00 to **8.50 in.** (76.2 to **215.9 mm**)
- Y Dimension*
 - 5.00 to **14.00 in.** (127.0 to **355.6 mm**)
- Append CR to LF
 - Yes
 - No**
- Enlarge A4 Prt Width
 - Off**
 - On
- BarDIMM*
 - Enable
 - Disable**
- FreeScape*
 - Off
 - ~
 - "
 - #
 - \$
 - /
 - \
 - ?
 - {
 - }
 - |

Imaging

- Image Orientation
 - Auto**
 - Vertical
 - Horizontal
- Zoom
 - Off**
 - Auto
- Print Position
 - Auto**
 - Center
 - Top Left
- Print Guarantee*
 - Off**
 - On
- Show Warnings
 - Off
 - Print**
 - Panel
- Print E-Mail Text
 - Off
 - On**
- Limit E-Mail Print*
 - Off**
 - On



Drawer 2 Size*

- A6
- A5
- A5R
- B5
- A4
- LTR
- LGL
- EXEC
- Mixed Sizes
- Custom Size
- Custom Size R
- 16K

Drawer 3 Size*

- A6
- A5
- A5R
- B5
- A4
- LTR
- LGL
- EXEC
- Mixed Sizes
- Custom Size
- Custom Size R
- 16K

Standard Paper Size

- A6
- A5
- B5
- A4
- LTR
- LGL
- EXEC
- Env. ISO-C5
- Env. Monarch
- Env. No.10
- Env. DL
- Index Card
- STMT
- 16K

Diff. Paper Tray

- Off
- On

Auto Selection

- Multi-Purpose Tray
 - Off
 - On
- Drawer 1
 - Off
 - On
- Drawer 2*
 - Off
 - On
- Drawer 3*
 - Off
 - On

Default Paper Type

- Plain
- Plain L
- Heavy 1
- Heavy 2
- Transparency
- Envelope
- Labels

2-Sided Printing

- Off
- On