**Menu Route Map** 

```
Default Screen After Startup/Restoration
Home, Secure Print, Status Monitor
  Home Screen Button Display Settings
   Set Display Order
  Deutsch, English, Español, Français, Italiano, Português, 日本語,
中文(繁體), 中文(简体), 한국어
      note UI Language
  English, Japanese, French, Spanish, German, Italian, Portuguese, Chinese (Simplified), Chinese (Traditional), Korean
Millimeter/Inch Entry Switch
 Gram/Pound Switch
Display Timing for Cart. Prep
           -Off
                 Custom
  Show Warnings
Off, On
 Action When Warning
   Low Cartridge Level
Continue Printing, Stop Printing
Display IP Address
```

```
lish Keyboard Layout
```

```
Time Zone
           (UTC-12:00) International Date Line West to (UTC-05:00)
           Eastern Time (US & Canada) to (UTC+14:00) Kiritimati Island
         ylight Saving Time Settings
             Start: Month, Week, Day
End: Month, Week, Day
 YYYY MM/DD, MM/DD/YYYY, DD/MM YYYY
  12 Hour (AM/PM), 24 Hour
 Auto Reset Time
      Set This Function
        Off
On
             Set Time

1 to 2 to 9 (min.)
Function After Auto Reset
  Default Function, Selected Function
Auto Sleep Time
 1 to 60 (min.)
Auto Sleep Daily Time
  Set This Function
                 (0:00 to 12:59 AM/PM)
     Set, for Auto Adjust Grad.
  Set This Function
          —On

└──(0:00 to 12:59 AM/PM)
  eep Mode Exit Time Set
  Set This Function
        Off
On
              (0:00 to 12:59 AM/PM)
```

```
Select Wired/Wireless LAN
 Wired LAN, Wireless LAN
    SSID Settings
      Enter Manually
            Security Settings
                     -WEP
                             WEP Key 1 to 4
                           -Shared Kev
                     -WPA/WPA2-PSK
                        Auto, AES - CCMP
    -WPS Push Button Mode
    WPS PIN Code Mode
      Power Save Mode
        nnection Information
         -Wireless LAN Status
         -Latest Error Information
         -Channel
         -SSID Settings
          -Security Settings
       Power Save Mode
 Use Direct Connection
                  Automatically Terminate Session
                       JOMERSON .

Off

On

Time Until Session Terminates
                 Access Point Mode Settings
                      se Custo.
Off
On
SSID

    Use Custom SSID

                     -Use Custom Network Key
                        Off
On
                Keep Enabled If SSID/Ntwk Key Spcfd
                Config. IP Address For Direct Conn.
                  192.168.22.1
 IPv4 Settings
               -Auto Acquire
                  -Auto Acquire
                       Off
                                   └─Off, DHCP
                               -- Auto IP
```

```
-IP Address: 0.0.0.0
                        -Subnet Mask: 0.0.0.0
                         Gateway Address: 0.0.0.0
                  Check Settings
              OHCP Option Settings
                  -Acquire Host Name

L—Off, On
                  DNS Dynamic Update
                  -Acquire Domain Name
                    └─Off. Or
                   Acquire WINS Server Address
                  -Acquire POP Server Address
                     Off, On
           -PING Command
         --- Use IPv6
                        Stateless Address Settings
                             - Stateless Address Settings
                              - Check Settings
                                Stateless Address
Prefix Length
                        DHCPv6 Settings
                           Use DHCPv6
                                └─Off. On
                                Stateful Address
Prefix Length
                            CP Option Settings
                             —Acquire DNS Server Address

—Off, On
                              -Acquire Domain Name
                                └─Off, On
       DNS Settings
            -IPv4 DNS Server Address Setting
              Primary DNS Server: 0.0.0.0
Secondary DNS Server: 0.0.0.0
                    Host Name
Domain Name
                     └─Use IPv4 Host/Domain
             DNS Dynamic Update Settings
                 −IPv4

L—DNS Dynamic Update
                         Off
On
DNS Dynamic Update Interval
                     L-DNS Dynamic Update
                           — Off
— On
                                    -Register Manual Address
                                    Register Stateful Address
                                    -Register Stateless Address
                                       Off, On
                                    -DNS Dynamic Update In:

-0 to 24 to 48 (hr.)
                ─IPv4
└─Use mDNS
                          Off
On
                                mDNS Name
                 -IPv6

Luse mDNS
                              On Use Same mDNS Name as IPv4
                                        Off __mDNS Name
        WINS Resolution
             On
On
                     WINS Server Address: 0.0.0.0
        PD Settings

Use LPD Printing
              └─Off. On
            -RX Timeout
              1 to 5 to 60 (min.)
       RAW Settings
        Use RAW Printing
              └─Off. On
            -RX Timeout
               1 to 5 to 60 (min.)
       WSD Settings
        Use WSD Printing
            -Use WSD Browsing
               └─Off, On
         --- Use Multicast Dis
              └─Off, On
      -Use HTTP
      Use IPSec
        └─Off. On
        ---LPD
            -RAW ____1 to 9100 to 65535
            -WSD Multicast Discovery
              └─1 to 3702 to 65535
            -HTTP
            -Multicast Discovery
              1 to 427 to 65535
            -POP3 ____1 to 110 to 65535
         -SNMP
               └─1 to 161 to 65535
      MTU Size
 SNMP Settings
      SNMPv1 Settings
        └─Off, On
       SNMPv3 Settings
Off, On
       Acquire Printer Mngt. Info. from Host
      Format Host Rsrcs. MIB to RFC2790
        └─Off. On
Use Dedicated Port
 Dedicated Port Auth. Method
  Mode 1, Mode 2
 Wait Time for Conn. at Startup
0 to 300 (sec.)
```

```
Communication Mode
                          Half Duplex, Full Duplex
                        -Ethernet Type
L—10BASE-T, 100BASE-TX, 1000BASE - T
           MAC Address
      Use IEEE 802.1X
         IPv4 Address Filter
                 Outbound Filter
                    └─Off, On
                   nbound Filter
                    └─Off, On
             Pv6 Address Filter
                 -Outbound Filter
                    └─Off, On
                  -Inbound Filter
                   └─Off, On
            MAC Address Filter
                 Outbound Filter
                   Off, On
                  Inbound Filter
          ale Cloud Print Settings
           Use Google Cloud Print
              Off, On
        Google Cloud Print Regist. Status
      Device Settings Manageme
      RMT-SW
      Initialize Network Settings
Settings marked with "*" may not be displayed depending on the options or other setting items
```

External Interface USB Settings Use as USB Device

Use USB Storage Device

Invert Screen Colors └─Off, On Brightness Message Display Time 1 to 2 to 5 (sec.)

```
Adjustment/Maintenance
     st Image Quality
       Quick Adjust
       auto Correction Settings
            Auto Adjust Image Regularly
              Off, When Turning Main Power ON, After Printing First Job
Correct Print Color Mismatch
          After Printing First Job, When Turning Main Power ON rect Print Color Mismatch
          Multi-Purpose Trav
                   -Adjust Vertically (Front Side)
-0.20" to 0.00" to + 0.20" (-5.0 to 0.0 to + 5.0 (mm))
                     Adjust Horizontally (Front Side)
                         -0.20" to 0.00" to + 0.20" (-5.0 to 0.0 to + 5.0 (mm))
                    Adjust Vertically (Back Side)
                      -0.20" to 0.00" to + 0.20" (-5.0 to 0.0 to + 5.0 (mm))
                    Adjust Horizontally (Back Side)
                      -0.20" to 0.00" to + 0.20" (-5.0 to 0.0 to + 5.0 (mm))
                  -Adjust Vertically (Front Side)
                      -0.20" to 0.00" to + 0.20" (-5.0 to 0.0 to + 5.0 (mm))
                    Adjust Horizontally (Front Side)
-0.20" to 0.00" to + 0.20" (-5.0 to 0.0 to + 5.0 (mm))
                    Adjust Vertically (Back Side)
                          -0.20" to 0.00" to + 0.20" (-5.0 to 0.0 to + 5.0 (mm))
                   -Adjust Horizontally (Back Side)
-0.20" to 0.00" to + 0.20" (-5.0 to 0.0 to + 5.0 (mm))
                  -Adjust Vertically (Front Side)
                         --0.20" to 0.00" to + 0.20" (-5.0 to 0.0 to + 5.0 (mm))
                    Adjust Horizontally (Front Side)
                      -0.20" to 0.00" to + 0.20" (-5.0 to 0.0 to + 5.0 (mm))
                    Adjust Vertically (Back Side)
                      -0.20" to 0.00" to + 0.20" (-5.0 to 0.0 to + 5.0 (mm))
                    Adjust Horizontally (Back Side)
                       -0.20" to 0.00" to + 0.20" (-5.0 to 0.0 to + 5.0 (mm))
               ecial Paper Processing
                      -Multi-Purpose Tray
                            └─Off. On
                          -Drawer 1

└──Off, On
                          −Drawer 2<sup>*</sup>

—Off, On
                        gh Surface Paper Mode
                          -Multi-Purpose Tray
-Off, On
                          -Drawer 1

└──<mark>Off</mark>, On
                   -Env. Flap Closing Prevention
                   Paper Wrinkle Correction
Off, Mode 1, Mode 2
                  Paper Curl Correction
Off, Mode 1, Mode 2
             Reduce Ppr. Sticking at Output
             High Humidity Mode
               Coff. On
            Low Humidity Mode
            Reduce Ghosting 1
                 Off, On
             Reduce Ghosting 2
             Regularly Clean Fix. Assembly
              Auto, Level 1, Level 2, Level 3 auto Clean Fixing Assembly
               Off
On


— Multi-Purpose Tray

└─Off, On
                         −Drawer 1


└─Off, On
                      Drawer 2
Off, On
            Rdc. Condens. (1-Sd->2-Sd Prt)
              Off, On
             Rdc Condens. (Consec 2-Sd Prt)
              Off. Mode 1. Mode 2
              Correct Uneven Gloss
             Corr. Void on Paper Back Side
               Off, On
```


```
Off, On
Corr. Img. Corrup. by Ppr. Dust Off, On
Prevent Fogging
Reduce Drum Streak
 └─Off. On
 Reduce Toner Flaking
Off, Mode 1, Mode 2
Reduce Toner Fixing Stain 1
Reduce Toner Fixing Stain 2
Auto Detect B&W/Color Orig.
 Mode 1, Mode 2
Rdc. Faint Print After Rplc. Cart.
 Off, On
```

Settings marked with "\*" may not be displayed depending on the options or other



## Function Settings





Menu Route Map

```
Binding Location
        Long Edge, Short Edge
      Gutter -1.90 to 0.00 to +1.90 (inches) or -50.0 to 00.0 to
      Offset Short Edge (Front)
       -2.00 to 0.00 to +2.00 (inches) or -50.0 to 00.0 to +50.0 (mm)
      Offset Long Edge (Front)
       -2.00 to 0.00 to +2.00 (inches) or -50.0 to 00.0 to +50.0 (mm)
     Offset Short Edge (Back)
       -2.00 to 0.00 to +2.00 (inches) or -50.0 to 00.0 to +50.0 (mm)
     Offset Long Edge (Back)
        -2.00 to 0.00 to +2.00 (inches) or -50.0 to 00.0 to
Auto Skip Error
 └─Off, On
Timeout
 5 to 15 to 300 (sec.)
 ersonality
 Auto, PS, PCL, PDF, XPS, Imaging Color Mode
Auto (Color/B&W), Black & White
 compressed Image Output
    Output, Display Error
Escape Tray Mode
Speed/Prt. Side Priority for 2-Sd
 Speed Priority, Print Side Priority
 Prioritize MP Tray
 └─Off, On
Check Paper Size in Tray
 └─Off, On
Recovery Printing
└─Off, On
UFR II
           Error Diffusion
Off, On
                 −Text

Resolution, Gradation
                  Graphics
Resolution, Gradation
     -Matching Method
       General, Perceptual, Colorimetric, Vivid Photo
      Gray Compensation
        Text/Graphics/Image
     -Paper Save
        Off. On
     -Paper Save
        Off, On
      Orientation
        Portrait Landscane
      Font Number
      Point Size 4.00 to 12.00 to 999.75 (point)
     -Pitch*
____0.44 to 10.00 to 99.99 (cpi)
      Form Lines
       5 to 60 to 128 (lines)
       PSMATH, PSTEXT, ROMANS, ROMANS, VNINTL.
            VNMATH, VNUS, WIN30, WINARB, WINBALT, WINCYR, WINGRK, WINL1, WINL2, WINL5

    Unit of Measure

        Millimeter, Inch
      X dimension 3 to 8 1/2 (inches) or 77 to 216 (mm)
        5 to 14 (inches) or 127 to 355 (mm)
     -Append CR to LF
     -Enlarge A4 Print Width
-Off, On
        Error Diffusion
             Off, On
            Resolution/Gradation
                Text
Resolution, Gradation
                 -Graphics
                   Resolution, Gradation
                  Image
Resolution, Gradation
      Matching Method
           -General, Perceptual, Colorimetric, Vivid Photo
     -Gray Compensation
        Text/Graphics/Image
               Off, On
     BarDIMM<sup>*</sup>
— Disable, Enable
     -FreeScape
        Off, ~, ", #, $, /, \, ?, {, },
      Job Timeout
     -Print PS Errors
       └─Off, On
     -Pure Black Text
          Off, On
     -RGB Source Profile
      CMYK Simulation Profile
     -Use Grayscale Profile
      Output Profile
        ☐ Text/Graphics/Image
              Normal, Photo, TR Normal, TR Photo
     -Matching Method
       Perceptual, Saturation, Colorimetric
      Halftones
        Error Diffusion
           -Resolution/Gradation
                 -Graphics
                   Resolution, Gradatio
                -Gravscale Conversion

SRGB. NTSC. Uniform RGB.
       PS Password Settings
       SystemParamsPassword
StartJobPassword
```

```
tion, Error Diffusion
                   Enlarge/Reduce to Fit Paper Size
                     └─Off. On
                  -Enlarge Print Area
                     └─Off. On
                   Print Comments
Off, Auto
                   Pure Black Text
                    └─Off, On
                   Black Overprint Off, On
                    RGB Source Profile
                     SRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4, None
                   CMYK Simulation Profile
                     JapanColor(Canon), U.S. Web Coated
                         v1.00(Canon), Euro Standard v1.00(Canon), None
                   Use Grayscale Profile
                     Off, On
                  -Output Profile
                            ■ Normal, Photo, TR Normal, TR Photo
                   Matching Method
                     Perceptual, Saturation, Colorimetric
                     Error Diffusion
                         Resolution/Gradation
                               -Graphics
-Resolution, Grada
                   Brightness<sup>*</sup>
—85 to 100 to 115 (%)
                    Composite Overprint
Off, On
                       -sRGB, NTSC, Uniform RGB
                    Matching Method
General, Perceptual, Colorimetric, Vivid Photo
                        −Error Diffusion

└─Off, On
                               -Text
└─Re
                               -Graphics
-Resolution, Gra
                    Text/Graphics/Image
                   Grayscale Conversion
                    irayscale Conversion.

— Text/Graphics/Image

— sRGB, NTSC, Uniform RGB
                       Off, On
         --- Network
             UFR II, UFR II (V4), PCL6, PCL6 (V4), PS
             ☐UFR II. UFR II (V4), PCL6, PCL6 (V4), PS
Settings marked with *** may not be displayed depending on the options, or other setting items.
```

```
Receive

Common Settings

Continue Print. When Cart. Low

Off, On

I-Fax Settings

Print on Both Sides

Off, On

RX Print Size

LTR, LGL, FOOLSCAP/FOLIO, OFICIO, LETTER

(Government), LEGAL (India),
FOOLSCAP (Australia), OFICIO (Brazil), OFICIO (Mexico),

A4
```

```
Access Files
            mon Settings
          Access Stored Files Settings
                     Change Default Settings (Memory Media Print)
                             Multi-Purpose Tray, Drawer 1, Drawer 2*
                            Number of Copies
                           2-Sided Printing
                             Off, Book Type, Calendar Type
                          -Set JPEG/TIFF Details
                                Brightness
Five Levels
                                 Original Type
                                             to Priority, Text Priority
                                 -Halftones
                                    Gradation Frror Diffusion
                            Set PDF Details

    Brightness

                                    Seven Levels
                                -N on 1
Off. 2 on 1, 4 on 1, 6 on 1, 8 on 1, 9 on 1, 16 on 1
                                  All Pages, Specified Pages
Enlarge/Reduce to Fit Paper Size
Off, On
                                    nlarge Print A
Off, On
                                  Print Comments
                                    Off, Auto
                                  Other Settings
                                              Error Diffusion
                                                    ─Text

—Resolution, Gradati
                                                     -Graphics
-Resolution, Grada
                                        -Pure Black Text
                                       Black Overprint
                                          └─Off. On
                                        RGB Source Profile
                                           SRGR Gamma 1.5 Gamma 1.8
                                               Gamma 2.4, None
                                         CMYK Simulation Profile
                                           ☐ JapanColor ( Canon ), U.S. Web
                                               Coated v1.00 ( Canon ), Euro Standard v1.00 ( Canon ), None
                                        - Use Gravscale Profile
```

```
Normal, Photo, TR
                                                    Normal, Photo, TR
                                              atching Method
                                                 Perceptual, Saturation,
Colorimetric
                                             composite Overprint
                                            Gravscale Conversion
                                             SRGB, NTSC, Uniform RGB
                                           Print Quality
                                                -Density
                                                          Yellow/Magenta/Cyar
17 Levels
                                                         Fine Adjust
                                                             Yellow/Magenta/C
                                                                yan/Black
                                                                 High/Med
                                                 −Toner Save

└─Off, On
                                                  -Gradation
                                                    High 1, High 2
                                                 Density Fine Adjustment
                                                  -Resolution
                                                    1200 dpi, 600 dpi
                                                  Special Smoothing Mode
                                                     Mode 1, Mode 2, Mode 3,
Mode 4, Mode 5, Mode 6
                                                  Toner Volume Correction
                                                    Standard, Gradation
Priority, Text Priority
                                                 -Line Control
                                                    Resolution Priority,
Gradation Priority
                                                  -Width Adjustment
                                                    Off
On
                                                  Advanced Smoothing
                                                         -Advanced Smoothing
-Off, Level 1, Level 2
                                                          Apply to Graphics
                                                         Apply to Text Off, On
                                                           on Smoothing
                                                         -Gradation Smoothing
                                                         Apply to Graphics Off, On
                                                          Apply to Images Off, On
                     Default Display Settings
                       Preview, Thumbnail, Details
                     -File Sort Default Settings
                       Name (Ascending), Name (Descending), Date/Time (Ascending), Date/Time (Descending)
                     -File Name Display Format

└─Short File Name, Long File Name
         Use Print Function
└── Off, On
Settings marked with **** may not be displayed depending on the options, or other
```

```
Secure Print

Use Secure Print

On

Restrict Printer Jobs

Off, On
Secure Print Deletion Time

10 to 30 to 240 (min.)
```

```
Management Settings

User Management

System Manager Information Settings

System Manager ID and PIN

System Manager ID

System Manager PIN

System Manager PIN

System Manager PIN

Department ID Management

Department ID Management

Off

On

Allow Print Jobs (Unknown IDs)
```

```
Device Management

Device Information Settings

Device Information Settings

Device Name

Location

Select Country/Region

United States (US), Canada (CA), Brazil (BR), Mexico (MX), Other

Display Job Log

Off, On

Use NFC

Off, On

Display Consumables Information (RUI/Toner Status)

Display Consmiss. Purch. Btn.(RUI)

Off, On

Toner Status Settings

Off

On

Off

On

Notify to Check Paper Settings

Off, On

Canon Genuine Mode

Off, On
```

```
License/Other

Register License

Remote UI Settings

Remote UI

Use Remote UI

Use TLS

Use TLS

Off

On

Restrict Access

Off

On

Remote UI Access PIN

Update Firmware

Via PC

Via Internet
```

```
Data Management
Import/Export
Import
Export
Enable Prod. Ext'd Survey Prog.
Off, On
Initialize Key and Certificate
Initialize Menu
Preferences
Adjustment/Maintenance
Function Settings
Initialize All
```

Initialize All Data/Setting